

**Filament lamp, E 10 (MES) base, 110 - 130 V****1.90.010.037/0000**

Ratings and operating life specifications generally refer to the lower rated voltage value.  
Operating life specifications of lamps refer to AC operation. With DC operation, these are reduced by about 40%.

**Electrical characteristics**

|               |             |
|---------------|-------------|
| Rated voltage | 110 - 130 V |
| Rated current | 0.018 A     |
| Rated power   | 2 W         |

**Other specifications**

|                          |        |
|--------------------------|--------|
| Diameter max.            | 11 mm  |
| Length                   | 30 mm  |
| Medium operating life AC | 1000 h |
| Socket                   | E 10   |
| ROHS compliant           | yes    |
| REACH compliant          | yes    |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

RAFI:

[1.90.010.037/0000](#)