

Filament lamp, W 2 x 4.6d base, 24 V**1.90.120.011/0000**

Ratings and operating life specifications generally refer to the lower rated voltage value.
Operating life specifications of lamps refer to AC operation. With DC operation, these are reduced by about 40%.

**Electrical characteristics**

Rated voltage	24 V
Rated current	0.04 A
Rated power	1.2 W

Other specifications

Diameter max.	5 mm
Length	20 mm
Medium operating life AC	7000 h
Socket	W 2 x 4,6d glass socket
ROHS compliant	yes
REACH compliant	yes

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RAFI:](#)

[1.90.120.011/0000](#)