

**Filament lamp, Bi-Pin T 1¼ base, 28 V****1.90.180.475/0000****Electrical characteristics**

Rated voltage	28 V
Rated current	0.03 A
Rated power	0.84 W

**Other specifications**

Diameter max.	4.3 mm
Length	10.5 mm
Medium operating life AC	5000 h
Socket	Bi-Pin T 1¼
ROHS compliant	yes
REACH compliant	yes

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

RAFI:

[1.90.180.475/0000](#)