

**LED W 2 x 4.6d superbright, blue, 24 V****1.90.690.364/0000****Electrical characteristics of LED**

Max. current, $I_F$	12 mA
LED wavelength typ.	630
Forward voltage typ. $U_F$ at $I_F$	24
LED breakdown voltage $U_R$ bei $I_F$	24
Light intensity	300

**Other specifications**

Socket	W 2 x 4.6d
Color	blue
Ambient temp. operating min.	-30 °C
Ambient temp. operating max.	+65 °C
Storage temperature min.	-35 °C
Storage temperature max.	+100 °C
ROHS compliant	yes
REACH compliant	yes

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

RAFI:

[1.90.690.364/0000](#)