

**LED Bi-Pin T 1, green, 3 V****1.90.691.027/0000****Electrical characteristics of LED**

Max. current, $I_F$	10 mA
LED wavelength typ.	635
Forward voltage typ. $U_F$ at $I_F$	2
Light intensity	9-33

**Other specifications**

Socket	Bi-Pin T 1
Color	green
Ambient temp. operating min.	-20 °C
Ambient temp. operating max.	+60 °C
Storage temperature min.	-30 °C
Storage temperature max.	+80 °C
Operating life	100,000 h
ROHS compliant	yes
REACH compliant	yes

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RAFI:](#)

[1.90.691.027/0000](#)