

## RF 19 - Signal indicator, 1 x 1-module

### 3.14.002.053/0000

For more information, see LEDs.



Suitable for RK 90 system design, illuminated for 2-module keycap.

#### General information

Colour of lens	yellow
Recommended key grid	23/x mm

#### Dimensions


Length	19.05 mm
Width	19.05 mm
Overall height	9.15 mm


#### Mechanical design

Mounting	THT soldering in PCB
Illumination	fully illuminated 2 LED
LED colour	yellow
LED type	2 mm


#### Other specifications

Ambient temp. operating min.	-25 °C
Ambient temp. operating max.	+70 °C
Environmental resistance	acc. to IEC 60068-2-14, -30, -33 and -78
Solderability / solder heat resistance	according to E DIN IEC 600 28-2-20
Wave soldering	260 °C max.
Manual soldering	350 °C / 5 sec. max.





0,5 x 2-module, yellow



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

RAFI:

[3.14.002.053/0000](#)