



H
G
F
E
D
C
B
A



Specifications 规格

Material 物料

Plastic Housing 塑胶外壳: LCP, UL94V-0

Contact Terminal 接触端子: Copper Alloy

Metallic Shell 金属外壳: SUS201

Plating 电镀

Underplating 底层电镀: 50μ" min. Nickel

Contact Area 接触面积: Gold (See ordering grid)

Solder Tails 焊接末端: 80μ" min. Matte Tin

Metallic Shell 金属外壳: 50μ" min. Nickel

Electrical 电气

Voltage Rating 电压额定值: 100 V AC/DC

Current Rating 电流额定值: 0.25A (Signal Pins 2,3,5,6,7,8,9)
1.8A (Power Pins 1,4)

Operating Temperature 工作温度: -55°C to +85°C

Contact Resistance 接触电阻值: 30 mΩ max.

Insulation Resistance 绝缘电阻值: 1000 MΩ min.

Dielectric Withstand Voltage 耐电压: 100V AC

Mechanical & Environmental 机械 & 环境

Mating Force 插入力: 35N max.

Unmating Force 拔出力: 10N min. initial, 8N min. after test

Durability 耐久性: 5,000 Cycles

Ordering Grid

USB1115-30-B-A

Contact Plating
30 = 30μ" Gold

Packing Options
A = Tape & Reel
(400 per reel)

Insulator Colour
B = Black


Part Number		Product Description	
USB1115		USB 3.0 Rec., Type A, Slim Type w/Cutaway Face, T-H,	
Drawing Date		Horizontal, Mid-Bottom Mount, 9 Pin, w/Outer Shell Stakes	
6th December 2013			
By	AJO	Tolerances (Except as Noted)	Units:
Detail	USB1115	Length	Metric (mm)
Revision	B	Angle	± 2°
Date	12/08/15	X.X ± 0.50	
		X.XX ± 0.38	
		X.XXX ± 0.20	
		X.XXX ± 0.10	



This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE

GCT
www.gct.co

Not to Scale
Drawn By AJO
Sheet No. 1/2



GCT
www.gct.co

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[GCT:](#)

[USB1115-30-B-A](#)