






Designed to comply with physical, electrical and environmental requirements of Micro USB Standard (USB2.0).




RECOMMENDED P.C.B LAYOUT

GENERAL TOLERANCE: ± 0.05

AS VIEWED FROM COMPONENT SIDE

Solder Area

Component Outline




Ordering Grid

USB3080 - 30 - XX - A

Contact Plating
30 = 30u" Gold

Packing Options
A = Tape & Reel
(1.5K per Reel)

Optional Plastic Locating Peg
00 = Without Peg
01 = With Peg (Standard)



Specifications 规格:

Materials 材料:

Plastic Housing 塑胶外壳: LCP, UL94V-0, Black; LCP, UL94V-0 黑色
Contact Terminal 接触端子: Copper Alloy 铜合金
Metallic Shell 金属外壳: Stainless Steel 不锈钢 SUS 304 T = 0.25mm

Plating 电镀:

Underplating 底层电镀: 50u" Nickel, 50u" 镍
Finish 表面处理: Contact Area 接触面积: 30u" Gold plating, 30u" 镀金
Solder Tails 焊接末端: Gold Flash 镀金
Metallic Shell 金属外壳: Matte Tin 雾锡

Electrical 电气规格:


Voltage Rating 电压额定值: 30 V AC
Current Rating 电流额定值: Signal(Pins 2,3,4)信号: 1.0 A.
Power (Pins 1,5)电源: 1.8A.
Operating Temperature 工作温度: -30°C to +85°C
Contact Resistance 接触电阻值: 30mΩ Max.
Insulating Resistance 绝缘电阻值: 1000MΩ Min.
Dielectric Withstand Voltage 耐电压: 500V AC/Minute

Mechanical 机械性规格:



Mating Force 插入力: 35N Max.
Unmating Force 拔出力: Initial 10N min.
Final 8N min after durability test.
Durability 耐久性: 10,000 Cycles 次插拔

Part Number		Product Description	
USB3080		Micro USB Receptacle, TYPE B, SMT, R/A, Bottom Mount, Optional Peg, With Shell Stakes	
Drawing Date			
04th April 2011			
By	CC	Tolerances (Except as Noted)	
Detail	USB3080 E PCN	Length	Angle
		X.X ± 0.40	X.X° ± 2°
		X.XX ± 0.25	X.XX° ± 1°
Revision	E2	X.XXX ± 0.05	X.XXX° ± 0.5°
Date	15/02/17		
		Units:	
		Metric (mm)	
			
		3rd Angle Projection	
			
			
		This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE	

GCT
www.gct.co




Products P/N	PCS/Reel	Reels/Carton	PCS/Carton
USB3080-30-XX-A	1500	4	6000



Detail F

Notes/注意:

1. Peeling off force of top tape: 0.1-1.3N
2. Part Conforms to EIA-481-C Standards 产品符合 EIA-481-C 标准
3. All dimensions in millimeters 所有尺寸均是毫米
4. 10 sprocket hole pitch cumulative tolerance ± 0.2 mm



Part Number		Product Description					
USB3080		Micro USB Receptacle, TYPE B, SMT, R/A, Bottom Mount, Optional Peg, With Shell Stakes					
Drawing Date							
04th April 2011							
By	CC	Tolerances (Except as Noted)		Units:			This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE
Detail	USB3080 E PCN	Length Angle		Metric (mm)			
Revision	E2						
Date	15/02/17			3rd Angle Projection			



This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE

GCT
www.gct.co

Not to Scale	Drawn By SA	Sheet No. 2/2
--------------	-------------	---------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[GCT:](#)

[USB3080-30-00-A](#)