





Ordering Grid

BJ302	XX	A	Request Samples and Quotation
No. of Contacts		Packing	
01 to 03		A = Tape & Reel	



Recommended PCB Layout
(Tolerance: ±0.05mm)
 Solder Area Component Outline



Specifications 规格

Material 物料

Insulator & Cover 绝缘体: LCP, UL 94V-0, Natural
Contact 端子: Copper Alloy

Plating 电镀

Contact 端子: Tin over Nickel

Electrical 电气

Current Rating 电流额定值: 8 Amp max.
Voltage Rating 电压额定值: 50 V
Contact Resistance 接触电阻值: 10 mΩ max.
Insulation Resistance 绝缘电阻值: 1000 MΩ min.
Dielectric Withstand Voltage 耐电压: 1500 V AC

Mechanical & Environmental 机械 & 环境

Operating Temperature 工作温度: -40°C to +105°C

Applicable Wire Range 适用线径规格:

Solid Wire 实心线: #24AWG to #18AWG
Stranded Wire 多股线: #22AWG to #20AWG
Max. Insulation OD 最大线径: Ø2.10mm

Note: Please see Product Specification document for more detailed information.

Part Number BJ302		Product Description 4.0mm Pitch, Surface Mount Wire Trap Connector	
Drawing Date 18th January 2015			
By AJO		Tolerances (Except as Noted) Length Angle	Units: Metric (mm)
Detail BJ302 X EOLN 20210318		X.X ± 0.35 X.XX ± 0.25	
Revision X			
Date 06/10/21			

This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE

www.gct.co

Not to Scale	Drawn By AJO	Sheet No. 1/2
--------------	-----------------	------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[GCT:](#)

[BJ302-02-A](#) [BJ302-01-A](#) [BJ302-03-A](#)