



Designed to comply with physical, electrical and environmental requirements of Micro USB Standard (USB2.0).



Specifications 规格

Material 物料

Plastic Housing 塑胶外壳: LCP, UL94V-0, Black
Contact Terminal 接触端子: Copper Alloy
Metallic Shell 金属外壳: Stainless Steel
SUS 304, T = 0.25mm

Plating 电镀






Underplating 底层电镀: 50μ" Nickel
Finish 表面处理: Contact Area 接触面积: 30μ" Gold plating
Solder Tails 焊接末端: Gold Flash
Metallic Shell 金属外壳: Matte Tin

Electrical 电气

Voltage Rating 电压额定值: 30 V AC
Current Rating 电流额定值: Signal (Pins 2,3,4): 1.0A.
Power (Pins 1,5): 1.8A.
Operating Temperature 工作温度: -30°C to +85°C
Contact Resistance 接触电阻值: 30mΩ max.
Insulating Resistance 绝缘电阻值: 1000MΩ min.
Dielectric Withstand Voltage 耐电压: 500V AC/Minute

Mechanical & Environmental 机械 & 环境



Mating Force 插入力: 35N max.
Unmating Force 拔出力: 10N min.
Durability 耐久性: 10,000 Cycles



Recommended PCB Layout

As viewed from component side
General Tolerance: ±0.05

■ Solder Area □ Component Outline



Ordering Grid

USB3065 - 30 - XX - A

Contact Plating
30 = 30u" Gold

Plastic Locating Peg
00 = Without (Standard)
01 = With



Request Samples
and Quotation

Packing Options
A = Tape & Reel
(1.5K per Reel)

Part Number		Product Description	
USB3065		Micro USB Receptacle, Type B, 5 Pin, SMT, Horizontal, Bottom Mount (Standard), Optional Plastic Locating Peg	
Drawing Date			
4th April 2011			
By	CC	Tolerances (Except as Noted)	
Detail	USB3065 E PCN	Length	Angle
		X.X ± 0.2	X.X" ± 2°
Revision	E2	X.XX ± 0.10	X.XX" ± 1°
		X.XXX ± 0.05	X.XXX" ± 0.5°
Date	13/12/16	Units: Metric (mm)	
			
			
			
		This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE	


GCT
www.gct.co

Not to Scale
Drawn By ASE
Sheet No. 1/2



Notes 注意:

1. Peeling off force of top tape: 0.1-1.3N
2. Part Conforms to EIA-481-C Standards 产品符合EIA-481-C标准
3. All dimensions in millimeters 所有尺寸均是毫米
4. 10 sprocket hole pitch cumulative tolerance ± 0.2 mm



Products P/N	PCS/Reel	Reels/Carton	PCS/Carton
USB3065-30-XX-A	1500	4	6000

Part Number		Product Description	
USB3065		Micro USB Receptacle, Type B, 5 Pin, SMT, Horizontal, Bottom Mount (Standard), Optional Plastic Locating Peg	
Drawing Date		4th April 2011	
By	CC	Tolerances (Except as Noted)	Units: Metric (mm)
Detail	USB3065 E PCN	Length	
Revision	E2	Angle	
Date	13/12/16		



This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE

GCT
www.gct.co

Not to Scale	Drawn By ASE	Sheet No. 2/2
--------------	--------------	---------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[GCT:](#)

[USB3065-30-00-A](#) [USB3065-30-01-A](#)