

Brackets and Enclosures

Model	Part No.	Length, inches	Width, inches	Height, inches	Type
GSC20	08-30466-020W	3.80	2.36	1.06	chassis and cover
GSx25	08-30466-0025	5.00	2.90	1.50	chassis and cover
GSM28	08-30466-0028	4.31	3.10	1.53	chassis and cover
GPx41	08-30466-1041	3.32	1.98	1.66	cover only
GLC40	08-30466-1040	6.00	3.27	1.70	chassis and cover
GPx40	09-33961-0001	6.00	3.27	1.70	chassis only
GPx40	08-30466-1040	6.00	3.27	1.70	chassis and cover
GPC50	08-30466-1055	6.50	4.20	2.25	chassis and cover
GLx50	08-30466-0050	5.00	2.90	1.50	chassis and cover
GPx55	08-30466-1055	6.50	4.20	2.25	chassis and cover
GLx65 single	08-30466-1065	5.00	3.30	1.50	chassis and cover
GLx65 multiple	08-30466-0065	5.00	3.30	1.85	chassis and cover
GLx75 single	08-30466-1075	5.75	3.50	1.85	chassis
GLx75 single	08-30466-2075	5.90	3.75	1.98	chassis and cover
GLx75 multiple	08-30466-1175	7.30	4.50	2.10	L bracket only
GLx75 multiple	08-30466-2175	7.30	4.50	2.10	L bracket and cover
GPx80	08-30466-1180	7.30	4.50	2.60	L-bracket and cover
GLx110	08-30466-2175	7.30	4.50	2.10	chassis and cover
GPFC110	08-30466-2110	6.30	3.75	1.75	cover
GPx130	08-30466-1130	8.50	4.50	2.25	cover
GPx140	08-30466-1140	8.50	4.50	2.25	cover
GLD140	09-140CF	8.50	4.50	1.95	cover w/fan
GLD150	08-30466-0150	7.00	4.50	1.95	cover
GLD150	09-150CF	7.00	4.50	2.45	cover w/fan
GPFX125	08-30466-2125	6.00	3.50	1.563	cover
GPFC160	09-160CF	7.00	4.50	1.75	cover w/fan
GPFM115	09-115CF	5.25	3.30	1.55	cover w/fan
GPC200	08-30466-1200	9.00	5.00	2.65	cover
GPC225	08-30466-1200	9.00	5.00	2.65	cover
GPFC250	09-250CF	8.00	5.00	1.81	cover w/fan
MS30/VBA	08-30466-1030	5.50	3.40	1.95	chassis and cover
RSx350	09-RBCover	9.50	5.00	3.59	cover w/fan
OLDER MODELS:					
MS110	08-30466-1110	8.80	4.95	2.45	chassis and cover
SDM45/SDS45	08-30466-0045	6.50	4.25	2.25	L-bracket
SDM80/SDS80	08-30466-0080	8.00	4.50	2.50	L-bracket
SDM110/SDS110	08-30466-0110	9.00	5.00	2.50	L-bracket
SDM140/SDS140	08-30466-0140	10.50	5.00	2.75	L-bracket
SDM200/SDS200	08-30466-0200	13.00	5.00	3.00	L-bracket
VCA	08-30466-1045	6.50	4.20	2.25	chassis and cover
VEA	08-30466-1080	8.00	4.60	2.55	chassis and cover
VFA	08-30466-0085	8.00	4.50	2.35	L-bracket
VFA	08-30466-2085	8.00	4.50	2.35	chassis and cover
VHA	08-30466-0100	8.50	5.00	2.75	L- bracket
VKA	08-30466-0125	10.50	5.00	2.75	L-bracket

NOTE: Other covers are available on a modified or custom basis. Please contact Condor for details.



Condor D.C. Power Supplies, Inc., 2311 Statham Parkway, Oxnard, CA 93033
800-235-5929 • 805-486-4565 • FAX 805-487-8911 • www.condorpower.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advanced Energy:](#)

[09-250CFG](#) [08-30466-1041G](#) [08-30466-0050G](#) [08-30466-0025G](#) [08-30466-1040](#) [08-30466-0025](#) [08-30466-2175](#)
[09-250CF](#) [09-115CF](#) [09-160CF](#) [08-30466-2110](#) [08-30466-0028](#) [08-30466-0050](#) [08-30466-020W](#) [08-30466-1041](#)
[08-30466-1055](#) [08-30466-1075](#) [08-30466-1080](#) [08-30466-1130](#) [08-30466-1140](#) [08-30466-1175](#) [08-30466-1180](#) [08-](#)
[30466-1200](#) [08-30466-2075](#) [08-30466-2125](#) [08-30466-1055G](#) [08-30466-0065G](#) [08-30466-020WG](#) [08-30466-1040G](#)
[09-160CFG](#) [09-115CFG](#) [08-30466-0028G](#) [09-150CFG](#) [08-30466-1065G](#) [09-140CFG](#) [08-30466-1075G](#) [09-33961-](#)
[0001G](#) [08-30466-0065](#) [18-30234-3306G](#) [08-30466-0200G](#)