Series 18X Hi-Amp Circuit Breaker



Auto, Manual & Switchable Reset Circuit Breakers

Specifications

Single Pole Thermal Type Breakers

Applications: Typically used in auxiliary and accessory circuits in truck, bus', RVs and marine systems. Others include battery chargers and DC audio systems. Series 181, 184 & 185 are sealed for engine compartment and bilge area applications.

Rating: 25-150A, 30Vdc; 48Vdc (Series 184 & 185)

Interrupt Rating: 3000A @ 30Vdc

Operating Temperature Rating: -25°F (-32°C) to 180°F (82°C) Storage Temperature Rating: -30°F (-34°C) to 300°F (149°C)

Materials: Black UL-rated 94V0 thermoset plastic. Thermoplastic elastomer stud insulators are provided on covered units with Early (ourface mount) bases.

provided on covered units with F-style (surface-mount) bases

Marking: Standard marking includes amp ratings and part numbers. Custom markings also available.

Termination: 1/4-28 threaded studs **Torque Rating:** 50 in-lbs (5.6N•m) max

Mounting Torque Rating: Panel or surface-mount options; 50 in-lbs (5.6N ⋅m) max. Threaded insert

option has a max torque of 25 in-lbs (2.8N•m).


Ingress Protection Rating: IP67


Features / Options: Series 184 & 185 have a unique reset mechanism which provides visual indication

of tripped condition. Series 185 also features a push-to-trip option

Compliances: SAE J1625; ABYC E-11; CE; SAE J1171 (ignition protected)

Dimensions - in(mm) (Dims. shown are for reference only. Consult factory for latest prints)







Flange mount gasket for thru-wall applications (option 07)

Part Numbering System

Series Rating Mounting Terminal Hdwr. Marking 1 8 181 - Type I, 30V F - Surface Mount 00 - Ship w/o nuts 0 - Blank cover 025 - 25 amps 1 - Standard Marking; Part Number, 183 - Type I*, 30V 030 - 30 amps P - Panel Mount 01 - Sems nuts installed 184 - Type III, 42V 035 - 35 amps 02 - Sems nuts shipped bulk Amp Rating 185 - Type III-PTT, 42V 03 - Stainless Steel Std. nuts & 181, 184, 185 Series - Top Surface 040 - 40 amps 050 - 50 amps washers installed 183 Series - Side Surface 060 - 60 amps 04 - Stainless Steel Std. nuts & S - Standard Ignition Protected 070 - 70 amps washers shipped bulk Marking 080 - 80 amps - Flange gasket & Sems nuts installed (Consult factory for special markings.) 090 - 90 amps (Panel Mount Only) *183 Available in Panel - Threaded insert and Sems nuts 100 - 100 amps Mount Only (Coverless) 110 - 110 amps installed 120 - 120 amps Stainless steel nuts and lockwashers 135 - 135 amps installed 150 - 150 amps 13 - Stainless steel Sems nut installed

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

184090F-03-1 185135P-01-1 185120F-01-1 184150F-03-1 185060F-04-1 185080F-01-1 181080F-01-1 184100P-07-1 181150F-03-1 185070F-13-1 184100P-01-1 184120P-01-1 185150F-01-S 185050F-01-S 184060F-03-1 185070F-01-1 184090F-01-S 184060F-01-S 184030F-00-1 181060F-01-1 185080F-01-S 184040F-01-S 181050P-01-1 181070P-07-0 181070P-01-1 185120P-01-1 185120P-07-1 184110F-01-S 185100F-01-1 185050F-01-1 187070P-04-1 187150P-04-1 18705P-04-1 181090F-01-1 185100F-01-S 18100F-01-1 185150P-01-S 184030F-01-S 184030F