

# BC Series



## Specifications

**Description:** Class CC fuse blocks for use with Class CC fuses (Cooper Bussmann LP-CC, KTK-R, and FNQ-R).

**Dimensions:** See Data Sheet 1105

**Poles:** 1 to 3

### Ratings:

Volts: — 600V

Amps: —  $\frac{1}{10}$ -30A

SCCR:— 200kA RMS Sym.

**Agency Information:** CE, UL Listed (Guide IZLT, File E14853), CSA (Class 6225-01, File 47235)

**Flammability Rating:** UL 94V0

**DIN Rail Adapters:** See page 413 for DRA-1 & DRA-2

## Catalog Numbers

| Terminal Type |                           |                |                                  |         |       |
|---------------|---------------------------|----------------|----------------------------------|---------|-------|
| Screw         | Screw with Quick Connect* | Pressure Plate | Pressure Plate w/ Quick Connect* | Box Lug | Poles |
| BC6031S       | BC6031SQ                  | BC6031P        | BC6031PQ                         | BC6031B | 1     |
| BC6032S       | BC6032SQ                  | BC6032P        | BC6032PQ                         | BC6032B | 2     |
| BC6033S       | BC6033SQ                  | BC6033P        | BC6033PQ                         | BC6033B | 3     |

**Data Sheet: 1105**

## BCCM Series

**Description:** 3-pole fuse block for use with (2) Class CC fuses and (1)  $\frac{13}{32}$ " x  $1\frac{1}{2}$ " fuse

## Catalog Numbers

| Catalog Numbers | Terminal Type                   |
|-----------------|---------------------------------|
| BCCM6033SQ      | Screw with Quick-Connect*       |
| BCCM6033PQ      | Pressure Plate w/Quick-Connect* |

\*Quick-connect terminal rated for 20A max.

## Recommended Cover Puller

- PF1-WH (White)
- PF1-BK (Black)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[BCCM6033PQ](#) [BCCM6033SQ](#) [PF1-BK](#)