

# Modular Type Fuse blocks for Class H & J Fuses



## Specifications

**Description:** 3-Pole only, modular type fuse blocks for Class H & J fuses with standard reinforced retaining clips.

### Ratings:

- Volts: — 250V (0-60A See Catalog Numbers table)  
          — 600V (35-60A See Catalog Numbers table)
- Amps: — 0-60A @ 250Vac/dc (See Catalog Numbers table)  
        — 35-60A@600V (See Catalog Numbers table)
- SCCR: — Class J 200kA, Class H 10kA

**Agency Information:** CE, UL Recognized, Guide IZLT2, File E14853, CSA Certified, Class 6225-01, File 47235.

## Class H & J Features and Benefits

- H & J modular fuse blocks provide three pole 30 and 60 amp ratings for specific client requirements for separate line and load fuse clip configurations.

## Typical Applications

- Up to 60A, space confined, control circuits

Fuse  
Holders  
& Blocks

| Catalog Numbers |                |            |       |      |          |  |
|-----------------|----------------|------------|-------|------|----------|--|
| Screw           | Pressure Plate | Fuse Class | Volts | Amps | Fig. No. |  |
| 11241-3SR*      | 11241-3PR*     | H          | 250   | 60   | 1        |  |
| 11242-3SR       | 11242-3PR      |            |       |      | 2        |  |
| 11241-3SR       | 11241-3PR      |            | 600   | 35   | 1        |  |
| 11242-3SR**     | 11242-3PR**    |            |       |      | 2        |  |
| 11239-3SR       | 11239-3PR      |            |       | 60   | 1        |  |
| 11240-3SR**     | 11240-3PR**    |            |       |      | 2        |  |
| 11241-3SR       | 11241-3PR      | J          |       | 35   | 1        |  |
| 11239-3SR*      | 11239-3PR*     |            |       | 60   | 1        |  |

Note: Order two blocks per fuse (matched or mixed.)  
\*11239 and 11241 have wire terminals and mounting holes located under fuse. (Figure 1)  
\*\*11240 and 11242 have wire terminals and mounting holes located at end of fuse. (Figure 2)



Figure 1



Figure 2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[11242-3SR](#) [11242-3PR](#) [11239-3SR](#) [11239-3PR](#) [11240-3SR](#) [11241-3PR](#) [11241-3SR](#) [11240-3PR](#)