

NDNLFD1-WH

Specifications

Description: Rail mount fuse holder.

Circuit Jumper: JF1, 2 circuits.

Fuse Size: ¼" X 1¼"
(Cooper Bussmann AGC, MDL or equivalent).

Poles: 1

Wire Range: AWG #8-22 Cu.

Ratings:

Volts: — 600V

- Amps: — 30A (NDND1 non-fused)
— 15A (NDNFD1, 600V/CSA, fused)
— 15A (NDNLFD1*fused, indicating)

*WH24 - 24V White, WH-90Vdc-600Vdc, 115Vac-600Vac White

Agency Information: CE, UL E62622; CSA LR15364.

Mounting Options: 35mm DIN rail, C-rail

Marking Tape: MT12-1-2

Torque Rating: 18 lb-in

Operating Temperature: 105°C

Agency Information: CSA File 15364

Catalog Numbers

Catalog

Number	Color	Indicator
NDNFD1-WH	White	NO
NDNLFD1-WH	White	90Vdc-600Vdc 115Vac-600Vac
NDNLFD1-WH 24	White	24V



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[NDNLF1-WH24](#) [NDND1-WH](#)