

Panel-Mount Fuseholder

For $1\frac{3}{32}" \times 1\frac{1}{2}"$ Fuses



Catalog Symbol: HPG

Panel-Mount

Ampere Rating: 30 Ampere

Voltage Rating: 600 Volts

Agency Approvals: U.L. Recognized, Guide IZLT2, File E14853


Flammability Rating: U.L. 94 VO

Temperature Rating (RTI): 150°C


General Information:

- Bayonet-type knob.
- For supplementary protection of transformers, relays, ballasts and small motors.
- Mount in $\frac{1}{2}"$ (12.7mm) knock-outs with locknut.
- Combination $\frac{1}{4}"$ (6.4mm) quick-connect/solder terminals.

Dimensional Data



Punched Mounting Hole



Electrical Ratings

Catalog Symbol	Amps	Volts AC	Fuse Description
HPG	30	600	Only side terminal is a quick-connect; rear terminal $\frac{3}{16}"$ longer than HPD.
HPG-EE	15	600	SC 0-15, $1\frac{3}{32}" \times 1\frac{5}{16}"$ fuses.
HPD	30	600	Rear terminal is $\frac{3}{16}"$ shorter than HPG

CE CE logo denotes compliance with European Union Low Voltage Directive (50-1000 Vac, 75-1500 Vdc). Refer to BIF document #8002 or contact Bussmann Application Engineering at 636-527-1270 for more information.

The only controlled copy of this BIF document is the electronic read-only version located on the Bussmann Network Drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Bussmann reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Bussmann also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

HPD