



Powering Business Worldwide

pe.eaton.com

Single Row Terminal Block

A102116B9R

UPC:051712326452

Dimensions:

- **Height:** .001 IN
- **Length:** 1.37 IN
- **Width:** .5 IN

Weight:.1 LB

Warranties:

- Not Applicable

Specifications:

- **Application:** industrial
- **Mounting:** Mount end
- **Special Features:** Break down voltage 1600V
- **Type:** Standard barrier
- **Voltage Rating:** 250V
- **Number Of Poles:** Six-pole
- **Operating Temperature:** -40° to 105°C
- **Options:** 0.187" QC
- **Wire Size:** #22-14 AWG Cu
- **Torque Rating:** 9 lb-in
- **Center Spacing:** 0.325 in
- **Screw Options:** Standard screw
- **Material:** Molded thermoplastic base, zinc plated phlslot wire-ready screw
- **Color:** Black
- **Connection:** #6-32 TPI screw, printed circuit, 0.187 in quick Connect
- **Terminal Material:** Printed circuit

Supporting documents:

- [Product Catalog](#)

Certifications: No Data

Product compliance:

- CE Marked



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[A102116B9R](#)