



Powering Business Worldwide

pe.eaton.com

Single Row Terminal Block

A495306L1L2

UPC:051712554671

Dimensions:

- **Height:** .001 IN
- **Length:** 6.61 IN
- **Width:** .87 IN

Weight:.1 LB

Warranties:

- Not Applicable

Specifications:

- **Application:** industrial
- **Mounting:** Insulator base, mount end
- **Special Features:** Break down voltage 6100V
- **Type:** Standard barrier
- **Voltage Rating:** 150V
- **Number Of Poles:** Six-pole
- **Operating Temperature:** -40° to 105°C
- **Options:** Marking options
- **Wire Size:** #16-8 AWG Cu
- **Torque Rating:** 9 lb-in
- **Center Spacing:** 0.562 in
- **Material:** Molded thermoplastic base, zinc plated slotted screw
- **Color:** Black
- **Terminal Material:** Stud top, #10-32 stud bottom

Supporting documents:

- [Product Catalog](#)

Certifications: No Data

Product compliance:

- CE Marked



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[A495306L1L2](#)