



Powering Business Worldwide

pe.eaton.com

Double Row Terminal Block

TB300-08L1L2QC6

UPC:051712295628

Dimensions:

- **Height:** .81 IN
- **Length:** 3.25 IN
- **Width:** 1.33 IN

Weight:.116 LB

Warranties:

- Not Applicable

Specifications:

- **Special Features:** Breakdown voltage 7500V
- **Type:** Barrier
- **Amperage Rating:** 30A
- **Voltage Rating:** 600V
- **Center Spacing:** 0.562 in
- **Material:** Molded thermoplastic base, tin-plated brass terminal, zinc-plated steel phillslot screw
- **Operating Temperature:** -40° to 130°C
- **Torque Rating:** 16 lb-in
- **Color:** Black
- **Number Of Poles:** Eight-pole

Supporting documents:

- [Product Catalog](#)

Certifications: No Data

Product compliance:

- CE Marked



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[TB300-08L1L2QC6](#)