

NetCommander PS2 Server Interface Unit (SIU)

MODEL NUMBER: B078-101-PS2



Features

- Needed to connect a PS/2 Server to a B070 / B072-Series NetCommander KVM switch via Cat5e cable
- Eliminates the need for thicker, heavier KVM cables
- Compact, lightweight design
- Plug and Play; no software required
- No power supply required
- Allows a Server/CPU to be located up to 100-ft. (30.5 m) away from the KVM switch
- To convert DisplayPort or HDMI computers to VGA, use adapters P134-06N-VGA-V2 or P131-06N

Highlights

- Needed to connect a PS/2 Server to a B070 / B072-Series NetCommander KVM switch via Cat5e cable
- Easy to install; no software needed
- No power supply needed
- Allows a recommended maximum distance of 100-ft. (30.5 m) from KVM to Server via Cat5e cable
- Compact and lightweight design

System Requirements

- Server or CPU with a HD15 port and (2) PS/2 type connections
- A B070 / B072-Series NetCommander Cat5 KVM Switch
- Cat5e/6 cable; up to 100-ft. (30.5 m)
- To convert DisplayPort or HDMI computers to VGA, use adapters P134-06N-VGA-V2 or P131-06N

Package Includes

- (x1) B078-101-PS2 PS/2 Server Interface Unit (SIU)

Specifications

OVERVIEW	
UPC Code	037332148438
Accessory Type	Server Interface Unit
Technology	Cat5/5e; PS/2; VGA/SVGA
Accessory Class	KVM Switch Accessories
INPUT	
Bus Powered	Yes
Product Length (ft.)	1.2
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side A - Connector 2	(2) MINI DIN-6 (FEMALE)



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	RJ45 (FEMALE)
Computer Keyboard and Mouse Interface	PS/2
Computer Monitor Interface	VGA
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	GREEN (RECEIVING POWER); ORANGE (SELECTED AS ACTIVE PORT)
PHYSICAL	
Color	Gray
Material of Construction	ABS
Shipping Dimensions (hwd / in.)	1.10 x 5.12 x 5.90
Shipping Dimensions (hwd / cm)	2.79 x 13.00 x 14.99
Shipping Weight (lbs.)	0.24
Shipping Weight (kg)	0.11
Unit Weight (lbs.)	0.22
Unit Weight (kg)	0.10
ENVIRONMENTAL	
Operating Temperature Range	-4° to 158°F (-20° to 70°C)
Storage Temperature Range	-4° to 158°F (-20° to 70°C)
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
Driver Required	No
Recommended Category Cable	N105 - SERIES CAT5E SHIELDED CABLES
STANDARDS & COMPLIANCE	
Product Certifications	EN 55022; EN 55024
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B078-101-PS2](#)