

2-Port HDMI Splitter - HDCP 2.2, 4K @ 60 Hz, HDR, TAA

MODEL NUMBER: B118-002-UHD-2



Transmits Ultra High Definition (UHD) 4K x 2K audio/video (A/V) from an HDMI source to two HDMI displays at the same time. Recommended for digital signage in classrooms, churches, office buildings, restaurants/bars, etc.

Description

The B118-002-UHD-2 2-Port 4K 3D HDMI Splitter transmits a UHD 4K @ 60 Hz (3840 x 2160) audio/video signal from an HDMI source, such as a Blu-ray player or computer, to two HDMI monitors, projectors or televisions at the same time. Ideal for classrooms, churches, offices, restaurants, bars, trade shows and anywhere else featuring 4K x 2K digital signage, the B118-002-UHD-2 is quick and simple to install with no software or drivers necessary.

Using standard 28 AWG HDMI cabling, this splitter can transmit a 4K (3840 x 2160) signal up to 15 feet (4.6 meters). It supports a wide range of audio formats, including DTS-HD, Dolby TrueHD, Dolby Digital Plus, and LPCM 7.1-channel surround sound, as well as 36-bit Deep Color (12 bits per channel). The Full 3D-compliant B118-002-UHD-2 also supports HDCP 2.2 for up-to-date content protection.

Note: The B118-002-UHD-2 sends the same image to all connected displays. If you would like to extend an image over multiple displays, you will need an MST hub, such as the B156-002-HD-V2.

Features

Transmits a 4K HDMI A/V Signal to 2 HDMI Displays Simultaneously

- Recommended for 4K digital signage in classrooms, churches, offices, restaurants, bars, trade shows, etc.
- Distributes A/V signals up to 15 ft. (4.6 m) when used with standard 28 AWG HDMI cable
- Supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video
- Compliant with HDCP 2.2 and EDID to ensure compatibility with latest A/V hardware
- Cascade up to 3 levels of splitters together to increase the number of connected monitors up to 32.

Supports the Most Up-To-Date Features and Formats

- Supports High Dynamic Range (HDR) for richer contrast and expanded color accuracy
- Full 3D
- DTS-HD, Dolby TrueHD, Dolby Digital Plus and LPCM 7.1-channel surround sound audio
- 36-bit Deep Color (12 bits per channel)
- Video amplifier bandwidth of 600 MHz/6 Gbps per channel (18 Gbps total)
- Lip sync pass-through, xvYCC and x.vColor

Easy to Use Almost Anywhere

- Plug-and-play operation with no software required for easy, immediate installation

Highlights

- Supports UHD resolutions up to 4K @ 60 Hz (3840 x 2160) for crystal-clear video
- Distributes A/V up to 15 ft. when used with 28 AWG HDMI cable
- Supports High Dynamic Range (HDR) for richer contrast and expanded color accuracy
- Expand the number of connected displays, up to 32, by cascading up to 3 levels of splitters together
- Plug-and-play operation with no software required for easy, immediate installation

System Requirements

- HDMI Source
- HDMI Monitor(s)

Package Includes

- B118-002-UHD-2 2-Port 4K 3D HDMI Splitter
- External power supply (Input: 100–240V, 50/60 Hz, 0.35A; Output: 5V 2A)
- International plug adapters (North America, Europe, U.K. and Australia)
- Mounting hardware
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

- Supports desktop use or wall-mounting using included hardware
- Power supply includes international plug adapters (North America, Europe, U.K. and Australia)

TAA-Compliant

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332200648
Product Type	Splitter
Device Compatibility	Monitor/HDTV
Technology	HDMI
Host Connector	HDMI (FEMALE)
VIDEO	
Max Supported Video Resolution	3840 x 2160 (4K) @ 60Hz
Max Supported Color Depth	36-bit Deep Color
HDR Support	Yes
3D Video Supported	Yes
AUDIO	
Audio Specification	DTS-HD, Dolby TrueHD, Dolby Digital Plus and LPCM 7.1 Channel Surround Sound
INPUT	
AC Power Adapter Plug(s)	NEMA 5-15P North America; CEE 7/16 Schuko; BS 1363 UK; AS/NZS 3112 Australia
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60HZ / 0.35A
AC Power Adapter Output Specs (V / A)	5V / 2A
AC Power Adapter Cord Length (ft.)	4.0
AC Power Adapter Cord Length (m)	1.2
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Bus Powered	No
Product Length (in.)	3.61
Product Length (ft.)	0.300
POWER	
Power Source Type	AC Adapter
Power Over Cable (PoC) Support	No



Powering Business Worldwide

TRIPP LITE
SERIES

AC Adapter	Input: 100-240V, 50/60Hz, 0.35A; Output: 5V, 2A, 4 ft
DC Barrel Plug	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
CONNECTIONS	
Number of Ports	2
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	(2) HDMI (FEMALE)
Connector Plating	Nickel
Input x Output	1 x 2
Daisy-chainable / Cascadable	Yes
Daisy-chainable / Cascadable Details	Up to 3 Levels for 32 Displays
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	(x1) Green (Power), (x2) Orange (Signal)
PHYSICAL	
Color	Black
Material of Construction	Metal
Cable Length (ft.)	0
Cable Length (m)	0.00
Rackmountable	Yes
Shipping Dimensions (hwd / in.)	2.17 x 7.24 x 6.46
Shipping Dimensions (hwd / cm)	5.51 x 18.39 x 16.41
Shipping Weight (lbs.)	0.99
Shipping Weight (kg)	0.45
Unit Dimensions (hwd / in.)	2.160 x 6.450 x 7.240
Unit Dimensions (hwd / cm)	5.49 x 16.38 x 18.39
Unit Packaging Type	Box
Unit Weight (lbs.)	0.187
Unit Weight (kg)	0.08
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0% to 85% RH, Non-Condensing
COMMUNICATIONS	



Powering Business Worldwide

TRIPP LITE
SERIES

EDID Compatible	Yes
IR Remote Extension Support	No
RS-232 Serial Extension Support	No
FEATURES & SPECIFICATIONS	
MST Support	No
HDCP Specification	2.2
Driver Required	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	CE; FCC; UL; cUL; TUV; CCC; PSE; C-Tick; GS; RoHS
Product Certifications	NOM (Mexico)
Product Compliance	RoHS; CE (Europe); REACH; WEEE; FCC (USA); Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[B118-002-UHD-2](#)