

## Multi-Device Charging Station, 48 USB Ports, iPad and Android Tablets, Black

MODEL NUMBER: CS48USB



Locking steel cabinet provides 2.4A USB charging, syncing, secure storage and cord management for up to 48 tablets and other USB devices.

### Features

#### Multi-Device Charging Station Accommodates up to 48 iPads and Other Tablets

The 120V CS48USB provides USB charging, device syncing, secure storage and cord management for as many as 48 iPad, Android, Surface, Kindle and other USB tablets, smartphones and devices. The connected devices' chargers connect to the charging station's 48 USB ports, which provide the fastest charging supported by each device up to 2.4A per port.

#### Locking Steel Enclosure Keeps Valuable Equipment Safe and Secure

Constructed from heavy-duty steel covered with a powder-coated finish, this tablet charging station provides safe, secure storage. Doors lock with the included keys to help prevent theft, damage and tampering. Flow-through ventilation helps protect against overheating, and the specially coated shelves help prevent device scratches and scuffs.

#### Supports Convenient Syncing

The USB sync uplink port connects to a host computer for wired or wireless syncing. The CS48USB can sync and charge devices at the same time, up to 1.5A charging per port during wired syncing.

#### Comes Fully Assembled for Immediate Use

The CS48USB ships fully assembled and supports mounting to a wall, desk, table, counter or floor. The front door opens 180 degrees to allow full access to the interior. Removable dividers accommodate thicker USB devices. A firmware upgrade port allows future updates. To move the charging station from room to room, you may convert it to a mobile cart using the optional CSHANDLEKIT accessory (sold separately). A detachable 10-foot (3.1-meter) power cord with NEMA 5-15P plug connects the charging station to an available AC outlet.

### Highlights

- 48 internal USB ports provide up to 2.4A apiece for fast charging of tablets
- Sturdy steel construction with locking doors that help prevent theft or tampering
- Supports charging of iPad, Android, Surface, Kindle and other USB tablets
- Flow-through ventilation helps prevent connected tablets from overheating
- 10 ft. cord with NEMA 5-15P plug allows great flexibility in reaching AC outlets

### Package Includes

- CS48USB Multi-Device Charging Station, Black
- Detachable AC input cord with NEMA 5-15P plug, 10 ft. (3.1 m)
- (2) Keys
- Owner's manual

## Specifications

OVERVIEW	
UPC Code	037332185433
Product Type	Multi-Device Charger



Powering Business Worldwide

TRIPP LITE  
SERIES

Charging Form Factor	Stationary Cabinet
Charger Functions	Charge; Secure; Sync
Device Compatibility	Tablet; Phone
Device Slots	48
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Voltage Compatibility (VAC)	110-240
Input Frequency	50 / 60 Hz (auto-select)
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
<b>POWER</b>	
Power Consumption (Watts)	224
<b>CHARGING</b>	
Number of Charging Ports	48
Total Charging Amps	120A
Total Charging Watts	600
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports Details	Pass through
Charging Ports / Amps	(48) 2.4A
Overcharge Protection	Yes
Charging Amps per Port	2.4A
<b>PHYSICAL</b>	
Color	Black
Material of Construction	Steel
Charging Station Form Factor	Stationary Cabinet
Shipping Dimensions (hwd / in.)	41.02 x 28.35 x 26.38
Shipping Dimensions (hwd / cm)	104.19 x 72.01 x 67.01
Shipping Weight (lbs.)	183.00
Shipping Weight (kg)	83.01
Slot Dimensions - Bottom (hwd / in.)	8.0 x 0,8 x 13,9
Slot Dimensions - Bottom (hwd / mm)	204 x 20,1 x 353.8



Powering Business Worldwide

TRIPP LITE  
SERIES

Slot Dimensions - Middle (hwd / in.)	8.0 x 0,8 x 13,9
Slot Dimensions - Middle (hwd / mm)	204 x 20,1 x 353.8
Slot Dimensions - Top (hwd / in.)	8.1 x 0,8 x 13,9
Slot Dimensions - Top (hwd / mm)	206 x 20,1 x 353.8
Unit Dimensions (hwd / in.)	35.630 x 23.620 x 21.570
Unit Dimensions (hwd / cm)	90.42 x 59.9 x 54.86
Unit Weight (lbs.)	150
Unit Weight (kg)	68.04
Number of Shelves	3
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Built-In Circuit Breaker	Yes
Cord Management	Yes
Overcurrent Protection	Yes
EMI/RFI Line Noise Protection	Yes
Flow-Through Ventilation	Yes
IP68 Rated	No
IP20 Rated	No
UV Sterilization	No
Locking	Yes
Lock Type	Key
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	NOM (Mexico); UL 60950-1
Product Compliance	RoHS; CE (Europe); EIA/ECA-310-E; REACH; FCC Part 15 Class B (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty
<b>CATEGORY PAGE FILTERS (Y/N ONLY)</b>	
External Receptacle	No

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[CS48USB](#)