

## 20-Device AC Charging Towers for Chromebooks - Open Frame, White, 2 Pack (40 Devices Total)

MODEL NUMBER: CST40AC



Provide high-speed AC charging and secure storage for 40 Chromebooks or tablets in a space-saving form factor designed for crowded rooms.

### Features

**Space-Saving Charging Stations Accommodate up to 40 Chromebooks and Tablets**The CST40AC consists of two CST20AC 20-device charging towers. These wall-anchored, floor-standing 120V charging stations provide high-speed AC charging, secure storage and cord management for as many as 40 Chromebooks, tablets and other mobile devices with a screen size up to 16 inches. These towers are recommended for schools, small/medium businesses, medical facilities, government agencies and anywhere else that uses Chromebooks or tablets on a daily basis.

**Space-Saving Form Factor Ideal for Mounting in Busy Classrooms**Designed to fit into classrooms and other areas with limited floor space, the two CST20AC units each feature a space-saving footprint of less than two square feet, perfect for small or crowded rooms. They attach to the wall with the included mounting brackets. They anchor to the wall at floor level, which allows access to younger children who need to charge their devices at school.

**Open Frame Design Allows Convenient Visibility without Unlocking the Door**An innovative open frame design allows you to see devices without unlocking and opening the half door in front. When checking at the end of the day to see whether all the Chromebooks or tablets have been returned, you can just glance at the charging stations from across the room for quick confirmation. The open sides allow cool air to easily flow through each tower, enhancing the performance of your devices and extending their life.

**High-Speed Charging with Plenty of Power to Keep Every Device at Full Capacity**Both charging towers come with a 20-outlet PDU already installed, giving you a dedicated NEMA 5-15R receptacle for every power adapter. Each tower has a charging capacity of 1440 watts, enough to charge all Chromebooks.

**Locking Steel Enclosure Keeps Valuable Equipment Safe and Secure**Constructed from heavy-duty steel covered with a white powder-coated finish, this charging tower provides safe, secure storage. Devices and their power adapters are stored in separate compartments. The front door and top panel both lock with included keys to help prevent theft, damage and tampering. Strategically placed bars down the sides prevent anyone from sliding a Chromebook out of the locked tower. The top panel allows access to the upper outlets and power adapters. A 15-amp circuit breaker protects the devices against overloads.

**Well-Organized to Avoid Confusing Cable Clutter**The CST40AC is compatible with a wide array of mobile devices, including Chromebooks, iPads, Android tablets, Surface tablets, Kindle e-readers and

### Highlights

- Space-saving footprint less than 2 sq. ft. ideal for crowded classrooms and back offices
- Open frame design allows visual access to contents without unlocking the front door
- Locking steel towers attach to the wall to discourage theft, damage and tampering
- Internal NEMA 5-15R outlets charge up to 40 devices with screens up to 16 in.
- 10-ft. (3.05 m) cords with NEMA 5-15P plugs allow great flexibility in placement near wall outlet

### Applications

- Charge up to 40 mobile devices in schools, businesses, government agencies and other organizations that rely on their daily use
- Recommended for Chromebooks, iPads, Android tablets, Surface tablets, Kindle e-readers and other mobile devices with screen sizes up to 16 in.

### Package Includes

- (2) CST20AC 20-Device AC Charging Towers, White
- (40) Power supply shelves
- (8) Wall-mount brackets
- (4) Keys
- Numbered stickers
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

other mobile devices with screen sizes up to 16 inches. Power cords are routed through cable management slots to keep them organized and prevent tangles. Each shelf comes with a numbered sticker for easy identification and is specially coated to help prevent device scratches and scuffs. The towers' 10-ft.(3.05 m) cords with NEMA 5-15P plugs allow great flexibility in placing the units near an AC wall outlet.

**Secure the Towers to a Wall or Move Your Devices from Room to Room**Mount the charging stations on a wall with the included brackets and user-supplied hardware. If you prefer the flexibility to roll the towers from one room to another, an optional caster kit (CSTCASTERKIT20, sold separately) includes four casters, mounting platform, handles and a locking rear door.

## Specifications

| OVERVIEW                           |                      |
|------------------------------------|----------------------|
| UPC Code                           | 037332240248         |
| Product Type                       | Multi-Device Charger |
| Charging Form Factor               | Tower                |
| Charger Functions                  | Charge; Secure       |
| Device Compatibility               | Chromebook           |
| Device Slots                       | 20                   |
| INPUT                              |                      |
| Nominal Input Voltage(s) Supported | 120V AC              |
| Input Connection Type              | AC                   |
| Voltage Compatibility (VAC)        | 120                  |
| Input Frequency                    | 60 Hz                |
| Input Plug Type                    | NEMA 5-15P           |
| Input Cord Length (ft.)            | 10                   |
| Input Cord Length (m)              | 3.05                 |
| OUTPUT                             |                      |
| Frequency Compatibility            | 60 Hz                |
| CHARGING                           |                      |
| Number of Charging Ports           | 40                   |
| Charging Method                    | AC                   |
| Charging Port Type                 | NEMA 5-15R           |
| Charging Ports Details             | Pass through         |
| Charging Ports / Amps              | (40) 15A             |
| Overcharge Protection              | No                   |
| Charging Amps per Port             | 15A                  |



Powering Business Worldwide

TRIPP LITE  
SERIES

| PHYSICAL                            |                                     |
|-------------------------------------|-------------------------------------|
| Color                               | White                               |
| Material of Construction            | Steel                               |
| Charging Station Form Factor        | Tower                               |
| Shipping Dimensions (hwd / in.)     | 22.20 x 17.80 x 52.83               |
| Shipping Dimensions (hwd / cm)      | 56.39 x 45.21 x 134.19              |
| Shipping Weight (lbs.)              | 300.00                              |
| Shipping Weight (kg)                | 136.08                              |
| Slot Dimensions (hwd / in.)         | 1.66 x 11.7 x 15.00                 |
| Slot Dimensions (hwd / mm)          | 42.10 x 297.60 x 383                |
| Unit Dimensions (hwd / in.)         | 52.830 x 17.800 x 22.200            |
| Unit Dimensions (hwd / cm)          | 134.18 x 45.212 x 56.39             |
| Unit Weight (lbs.)                  | 87.560                              |
| Unit Weight (kg)                    | 39.72                               |
| Number of Shelves                   | 40                                  |
| Assembly Required                   | Yes                                 |
| FEATURES & SPECIFICATIONS           |                                     |
| Antimicrobial                       | No                                  |
| Built-In Circuit Breaker            | Yes                                 |
| Cord Management                     | Yes                                 |
| Overcurrent Protection              | Yes                                 |
| EMI/RFI Line Noise Protection       | No                                  |
| Flow-Through Ventilation            | Yes                                 |
| IP68 Rated                          | No                                  |
| IP20 Rated                          | No                                  |
| UV Sterilization                    | No                                  |
| Locking                             | Yes                                 |
| Lock Type                           | Key                                 |
| STANDARDS & COMPLIANCE              |                                     |
| Product Certifications              | CSA (Canada); IEC/EN 62040; UL 1778 |
| Product Compliance                  | RoHS                                |
| WARRANTY & SUPPORT                  |                                     |
| Product Warranty Period (Worldwide) | 2-year limited warranty             |

CATEGORY PAGE FILTERS (Y/N ONLY)

|                     |    |
|---------------------|----|
| External Receptacle | No |
|---------------------|----|

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[CST40AC](#)