


## Dual Vertical Flat-Screen Desk Stand/Clamp Mount, 15 in. to 27 in. Flat-Screen Displays

MODEL NUMBER: DDR1527SDC



VESA-compliant unit for mounting 2 flat-panel displays above your desk, table or workstation's surface to free up valuable space. One-touch adjustment for customizing the displays' viewing angles for comfortable viewing.

### Description

The VESA-compliant DDR1527SDC Dual Vertical Flat-Screen Desk Stand/Clamp Mount frees up valuable space on your desk, table or workstation by allowing you to mount two flat-panel displays on a vertical pole. Ideal for home or office, the DDR1527SDC fits most flat-panel displays from 15 to 27 inches. You can use it as a desktop stand or clamp it to a flat surface up to three inches thick.

One-touch adjustment lets you optimize viewing angles and improve ergonomics as you switch tasks during the day. Adjust the dual mounting plates independently for angle and height to give you maximum flexibility in positioning your displays to fit your environment and comfort level. A 20° swivel and -20° to +20° tilt capability minimizes glare and provides comfortable viewing from multiple angles. A 360° rotation lets you view your displays in portrait and landscape orientations.

Each mounting plate supports flat-panel displays up to 18 lbs (8.2 kgs). The durable all-metal frame with scratch-resistant powder-coated finish tolerates frequent handling and blends with any décor. Included cable clamps organize cables and secure them to the vertical pole to prevent clutter. Mounting hardware is included. Conforms to VESA-compliant displays with hole patterns of 75 x 75 mm and 100 x 100 mm.

### Features

**Compatible with Most Desks, Tables and Workstations** Functions as either a desktop stand or clamp-on mount - both mounting options included Mounts 2 flat-panel displays from 15 to 27 in. on a vertical pole Dual mounting plates adjust independently for angle and height Ideal for home and office use Clamps to flat surface up to 3 in. thick

**Convenient One-Touch Adjustment** 20° swivel and -20° to +20° tilt capability provide comfortable viewing from multiple angles Full 360° rotation in both portrait and landscape orientations

**Durable Metal Construction** Each mounting plate supports displays up to 18 lbs (8.2 kgs) Scratch-resistant powder-coated finish blends with any décor Mounting hardware included Cable clamps organize cables and reduce clutter

**VESA Compliance** Conforms to VESA-compliant universal mounting hole patterns

## Specifications

### Highlights

- Functions as either a desktop stand or clamp-on mount
- Fits most flat-panel displays from 15 to 27 in.
- One-touch adjustment for easy viewing from multiple angles
- -20° to +20° tilt, 20° swivel and 360° rotation capability
- Supports displays up to 18 lbs (8.2 kgs) each

### Package Includes

- Pole
- (2) Mount assemblies with VESA plate
- Desktop base
- Clamp
- (2) Locating rings
- Top cap
- Hex key, 3 mm
- Hex key, 4 mm
- Hex key, 5 mm
- (8) M4 x 12 mm screws
- (8) M4 x 30 mm screws
- (3) M6 x 15 mm screws
- (8) Spacers
- (2) Cable clamps
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

OVERVIEW	
UPC Code	037332190574
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Mounting Location	Desktop; Desk Clamp
Degrees of Motion	-20/+20 Tilt; 20 Swivel; 360 Rotate
Minimum Screen Size (in.)	15
Minimum Screen Size (cm)	38.1
Maximum Screen Size (in.)	27
Maximum Screen Size (cm)	68.58
Maximum Weight Capacity (lbs.)	18
Maximum Weight Capacity (kg)	8
Number of Displays	2
Shipping Dimensions (hwd / in.)	13.80 x 13.00 x 5.40
Shipping Dimensions (hwd / cm)	35.05 x 33.02 x 13.72
Shipping Weight (lbs.)	14.25
Shipping Weight (kg)	6.46
Unit Dimensions (hwd / in.)	23.600 x 17.700 x 10.900
Unit Dimensions (hwd / cm)	60 x 45 x 28
Unit Weight (lbs.)	15.80
Unit Weight (kg)	7.17
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	Yes
Tools Necessary	Yes
Security Lock	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; REACH



Powering Business Worldwide

TRIPP LITE  
SERIES

WARRANTY & SUPPORT

Product Warranty Period (Worldwide)	5-year limited warranty
--	-------------------------

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[DDR1527SDC](#)