

EM2413 Series**EuroMag Terminal Blocks**

Pluggable Block with Flanges (Mates with EM2201 Series); 3.50 Centers

SPECIFICATIONS

Rating: 10A, 300V

Center Spacing: 0.138" (3.50mm)

Wire Range: #16-26 AWG

Housing Material: UL rated 94V0 Thermoplastic

Contact Material: Brass Tin-Plated

Cage Material: Brass, Nickel-Plated

Screw Size: M2.0 Zinc-Plated Steel

Operating Temperature: 105°C (221°F) max., -40°C (-40°F) min.




Torque Rating: 3.0 lb-in.

Construction: Mold-to-Length

Agency Information: eus File E62622; CE Certified



EM241307

Dimensions - mm (in)

Poles	L (mm)
2	17.4
3	20.9
4	24.4
5	27.9
6	31.4
7	34.9
8	38.4
9	41.9
10	45.4
11	48.9
12	52.4

To convert to inches, divide by 25.4

Part Numbering System

Series

of Poles

EM2413

02 12

02 to 12

Mating Header: EM2201 pg. 77

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[EM241307](#) [EM241311](#) [EM241306](#) [EM241308](#) [EM241304](#) [EM241305](#) [EM241302](#) [EM241310](#) [EM241309](#)
[EM241312](#) [EM241303](#)