


EM3226 Series**EuroMag Terminal Blocks**

35° Angle, 7.62 Centers; Modular

SPECIFICATIONS**Rating:** 16A, 300V**Center Spacing:** 0.30" (7.62mm)**Wire Range:** #12-26 AWG**Housing Material:** UL rated 94V0 Thermoplastic**Contact Material:** Brass Tin-Plated**Cage Material:** Brass, Nickel-Plated**Screw Size:** M2.6 Zinc-Plated Steel**Operating Temperature:** 105°C (221°F) max., -40°C (-40°F) min.**Torque Rating:** 5.0 lb-in.**Recommended PCB Hole Diameters:** 0.055" (1.40mm)**Construction:** Modular design features dovetails for interlocking to achieve longer lengths**Agency Information:** cULus File E62622; CE Certified

EM322605

Dimensions - mm (in)

Poles	L (mm)	Poles	L (mm)
2*	15.24	14	106.69
3*	22.86	15	114.31
4	30.48	16	121.93
5	38.10	17	129.55
6	45.72	18	137.17
7	53.34	19	144.79
8	60.96	20	152.41
9	68.58	21	160.03
10	76.20	22	167.65
11	83.82	23	175.27
12	91.44	24	182.89
13	99.07		

* Mold-to-Length

To convert to inches, divide by 25.4

Part Numbering System

Series

of Poles

EM3226

02 to 24

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[EM322606](#) [EM322607](#) [EM322608](#) [EM322609](#) [EM322623](#) [EM322605](#) [EM322611](#) [EM322612](#) [EM322617](#)
[EM322622](#) [EM322615](#) [EM322613](#) [EM322624](#) [EM322614](#) [EM322604](#) [EM322616](#) [EM322620](#) [EM322610](#)
[EM322602](#) [EM322603](#) [EM322618](#) [EM322619](#) [EM322621](#)