

## EEI-NEMA Type K & T and Type H & N

### FL: Type H and EEI-NEMA Type K & T Fuses

#### Specifications

**Description:** Medium voltage fuses: Type H (high surge), EEI-NEMA Type K (fast-acting), EEI-NEMA Type T (slow-acting).

#### Ratings:

Amps: — 1-200A  
(See Catalog Numbers tables)



#### Features and Benefits

- Wide range of EEI-NEMA type fuse links for use in open fuse cutouts
- Voltage ratings up to 27kV.
- Can be coordinated with other overcurrent protective devices for sectionalizing to isolate feeder branches.

#### Typical Applications

- Medium Voltage Fused Cutouts

#### High-Surge Type H Fuses

High-surge, Type H fuses are manufactured in ratings of 1, 2, 3, 5, and 8A. They have been developed principally for primary fusing of small-sized transformers. Type H links are manufactured in the universal buttonhead design.

#### Type N Fuses

Type N fuses conform to previous NEMA standards and have been superseded by Type K and T links. Type N fuses are manufactured in the universal button design in ratings of 5 through 200A for use in NEMA standard dimensioned cutouts rated through 27kV.

### Catalog Numbers

#### EEI-NEMA and High-Surge Universal Tin Element

##### Fuses for Cutouts — Rated to 27kV

Non-Removable Button-Head For Standard Open Or Enclosed Cutouts

Catalog Numbers	EEI-NEMA Type K (Fast)	EEI-NEMA Type T (Slow)	Amps
FL11H1	FL11K1	FL11T1	1
FL11H2	FL11K2	FL11T2	2
FL11H3	FL11K3	FL11T3	3
FL11H5	FL11K5	FL11T5	5
—	FL11K6	FL11T6	6
FL11H8	FL11K8	FL11T8	8
—	FL11K10	FL11T10	10
—	FL11K12	FL11T12	12
—	FL11K15	FL11T15	15
—	FL11K20	FL11T20	20
—	FL11K25	FL11T25	25
—	FL11K30	FL11T30	30
—	FL11K40	FL11T40	40
—	FL11K50	FL11T50	50
—	FL11K65	FL11T65	65
—	FL11K80	FL11T80	80
—	FL11K100	FL11T100	100
—	FL11K140	FL11T140	140
—	FL11K200	FL11T200	200

Removable Button-Head For Cutouts Requiring Removable-Button Links\*

Catalog Numbers	EEI-NEMA Type K (Fast)	EEI-NEMA Type T (Slow)	Amps
FL3K1	FL3T1		1
FL3K2	FL3T2		2
FL3K3	FL3T3		3
FL3K5	FL3T5		5
FL3K6	FL3T6		6
FL3K8	FL3T8		8
FL3K10	FL3T10		10
FL3K12	FL3T12		12
FL3K15	FL3T15		15
FL3K20	FL3T20		20
FL3K25	FL3T25		25
FL3K30	FL3T30		30
FL3K40	FL3T40		40
FL3K50	FL3T50		50
FL3K65	FL3T65		65
FL3K80	FL3T80		80
FL3K100	FL3T100		100
FL3K140	FL3T140		140
FL3K200	FL3T200		200

\*Adapter-type removable-button links with ferrule adapter to convert to double-leader links are available in K and T types. Order by description.

#### EEI-NEMA Type K Universal Silver-Element Fuses for Cutouts — Rated through 27kV

Non-Removable Button-Head For Standard Open Or Enclosed Cutouts

Catalog Numbers	EEI-NEMA Type K	Amps
FL12K8		8
FL12K10		10
FL12K12		12
FL12K15		15
FL12K25		25
FL12K50		50

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Eaton:

[FL11K100](#) [FL3T100](#) [FL3K12](#) [FL12K15](#) [FL3K3](#) [FL3K30](#) [FL11K140](#) [FL3T20](#) [FL11K20](#) [FL3K65](#) [FL3K20](#) [FL3K6](#)  
[FL3T25](#) [FL3K15](#) [FL3K80](#) [FL11K15](#) [FL11K6](#) [FL11K25](#) [FL11T50](#) [FL11K2](#) [FL3K2](#) [FL11K5](#) [FL11T5](#) [FL11K40](#)  
[FL3T15](#) [FL11K10](#) [FL3T50](#) [FL11T65](#) [FL11T2](#) [FL12K10](#) [FL3K5](#) [FL3K100](#) [FL12K25](#) [FL3T40](#) [FL11T40](#) [FL3K8](#)  
[FL3T80](#) [FL11K80](#) [FL11K65](#) [FL3K50](#) [FL11T6](#) [FL3K1](#) [FL11K12](#) [FL11K200](#) [FL11K30](#) [FL11K50](#) [FL3K25](#) [FL12K50](#)  
[FL3K10](#) [FL3T65](#) [FL11T8](#) [FL11K8](#) [FL11T80](#) [FL11K3](#) [FL11T1](#) [FL11T3](#) [FL3T6](#) [FL3T10](#) [FL3K40](#) [FL3K200](#) [FL3T8](#)  
[FL11K1](#) [FL3K140](#) [FL3T3](#) [FL3T5](#) [FL3T1](#)