



Powering Business Worldwide

pe.eaton.com

Eaton Bussmann series high speed cylindrical fuse

FWC-30A10F

UPC:051712370851

Dimensions:

- **Height:** .46 IN
- **Length:** 20.866 IN
- **Width:** 15.354 IN

Weight:.0207 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** FWC, Ferrule style
- **Application:** DC common bus, DC drives, power converters/rectifiers, reduced voltage starters
- **Voltage Rating:** 500 Vac/dc (35-800A only)
- **Interrupt Rating:** 200 kAIC Vac, 50 kAIC at 700 Vdc
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Current Rating:** 30A RMS
- **Pre Arc (I₂T):** 95
- **Clearing (I₂T):** Clearing at 600V: 600
- **Connection:** Ferrule end X ferrule end
- **Watt Losses:** 7.5W

Supporting documents:

- [Product Catalog](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance:

- CE Marked



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[FWC-30A10F](#)