



Powering Business Worldwide

pe.eaton.com

Double Row Terminal Block

TB200-1100

UPC:051712274364

Dimensions:

- **Height:** 8.5 IN
- **Length:** 7 IN
- **Width:** 4 IN

Weight: 3.58 LB

Warranties:

- Not Applicable

Specifications:

- **Special Features:** Breakdown voltage 4800V
- **Type:** Barrier
- **Amperage Rating:** 30A
- **Voltage Rating:** 300V
- **Center Spacing:** 0.437 in
- **Material:** Molded thermoplastic base, tin-plated brass terminal, screws shipped bulk
- **Operating Temperature:** -40° to 130°C
- **Torque Rating:** 9 lb-in
- **Color:** Black
- **Number Of Poles:** 11-pole

Supporting documents:

- [Product Catalog](#)

Certifications: No Data

Product compliance:

- CE Marked
- RoHS Compliant



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[TB200-1100](#)