



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Double Row Terminal Block

TB200HB-06L1L2QC4

UPC:051712241656

### Dimensions:

- **Height:** .75 IN
- **Length:** 2.51 IN
- **Width:** 1.37 IN

**Weight:**.5 LB

### Warranties:

- Not Applicable

### Specifications:

- **Special Features:** Breakdown voltage 4800V
- **Type:** High barrier
- **Amperage Rating:** 30A
- **Voltage Rating:** 600V
- **Center Spacing:** 0.437 in
- **Material:** Molded thermoplastic base, tin-plated brass terminal, zinc-plated steel phillslot screw
- **Operating Temperature:** -40° to 130°C
- **Torque Rating:** 9 lb-in
- **Color:** Black
- **Number Of Poles:** Six-pole

### Supporting documents:

- [Product Catalog](#)

**Certifications:** No Data

### Product compliance:

- CE Marked



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[TB200HB-06L1L2QC4](#)