



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Eaton Bussmann series time-delay in-line fuse

**BK/GMQ-3-2/10**

**UPC:**051712106139

### Dimensions:

- **Height:** 2.25 IN
- **Length:** .001 IN
- **Width:** .72 IN

**Weight:**.013 LB

### Warranties:

- Not Applicable

### Specifications:

- **Type:** Low voltage
- **Application:** in-line lightning ballast protection
- **Amperage Rating:** 3-2/10A
- **Voltage Rating:** 300V or less
- **Interrupt Rating:** 10 kAIC
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Used With:** HLQ-3-2/10 holder
- **Material:** Ceramic tube
- **Mounting:** Panel
- **Quantity:** Bulk 100

### Supporting documents:

- [Product Catalog](#)

**Certifications:** No Data

### Product compliance:

- CE Marked



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

BK/GMQ-3-2/10