

Monitor Riser for Desk, 14 x 9 in. - Height Adjustable, Metal, Black

MODEL NUMBER: MR1411M



Computer monitor stand lifts your monitor incrementally up to 5.5 in. above your workstation surface to help ease eye and neck strain.

Features

Maintenance-Free Computer Monitor Stand Raises Your Screen for Comfortable Viewing This desk monitor riser allows you some flexibility in placing your monitor for maximum comfort. The legs adjust to heights of 3.9 inches (100 millimeters), 4.7 inches (120 millimeters) and 5.5 inches (140 millimeters), so you can view your monitor while lessening strain on your eyes and neck. Lifting your monitor also frees up valuable space on your desk, table or counter at home, school or office.

Rugged Metal Construction Supports Up to 44 Pounds The rectangular metal platform measures 14 x 9 inches and supports monitors, laptops, printers, small televisions and other devices weighing up to 44 pounds. The platform is ventilated to allow proper airflow and help keep your monitor cool. Rubber feet attached to the legs secure the riser in place on a smooth surface. The monitor stand riser assembles in just a few seconds with no tools or permanent mounting required.

Highlights

- Computer monitor riser adjusts to heights of 3.9 in., 4.7 in. and 5.5 in.
- Eases eye and neck strain while clearing valuable space on your desk or table
- Rectangular metal platform supports monitor or other devices up to 44 lb.
- Ventilated surface allows proper airflow to help keep your monitor cool
- Desktop computer stand assembles easily in just a few seconds with no tools required

Applications

- Elevate your monitor up to 5.5 in. for more comfortable viewing and to free up desktop space
- Hold a monitor or small television in position without permanently mounting it
- Adjust screen height to match comfort levels of different users

Package Includes

- MR1411M Monitor Riser for Desk, 14 x 9 in.
- (4) Legs w/rubber feet
- Assembly instructions

Specifications

OVERVIEW	
UPC Code	037332231154
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Metal
Mounting Location	Desktop
Maximum Weight Capacity (lbs.)	44
Maximum Weight Capacity (kg)	20



Powering Business Worldwide

TRIPP LITE
SERIES

Number of Displays	1
Shipping Dimensions (hwd / in.)	1.18 x 9.70 x 15.40
Shipping Weight (kg)	1.27
Unit Dimensions (hwd / in.)	5.510 x 9.200 x 14.400
Unit Dimensions (hwd / cm)	14 x 23.4 x 36.6
Unit Weight (lbs.)	2.2
Unit Weight (kg)	1.00
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	No
Security Lock	No
Height Adjustable	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; RoHS3; CE (Europe); REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[MR1411M](#)