

Important Note

This cable can only be used to stream 4K video when used with a Thunderbolt-3 enabled monitor. A USB-C or DisplayPort input will not support video transmission.

Thunderbolt 3 Active Cable (M/M) - 40 Gbps, 5A 100W Power Delivery, 4K/60 Hz, 2M (6.56 ft.), Black

MODEL NUMBER: MTB3-02M-5A-AB



Connects 2 Thunderbolt 3 devices, including MacBooks and Chromebooks, for charging them or transmitting 4K video at 40 Gbps speeds.

Features

Active Cable Connects Thunderbolt 3 Devices, Including MacBooks and Chromebooks This Thunderbolt 3 cable allows you to connect one Thunderbolt 3-enabled device to another, including MacBooks, Ultrabooks, Chromebooks, external hard drives and docking stations. It transmits full 4K x 2K (3840 x 2160 at 60 Hz) DisplayPort video when used with Thunderbolt 3-enabled monitors. The cable's two-meter length makes it easy to carry in your briefcase or laptop bag for quick video connections and file transfers on the go.

Charges Devices and Transfers Data 4 Times Faster Than USB 3.1 Gen 2 The MTB3-02M-5A-AB supports bidirectional Thunderbolt 3 data transfer speeds up to a sizzling 40 Gbps, which is four times as fast as USB 3.1 Gen 2, making it an ideal cable for downloading 4K video files and transmitting them to a 4K monitor or television with a Thunderbolt 3-enabled input. Transceivers in each connector regulate the transfer of data throughout the entire length of the active cable. The PD Charging 2.0 cable also provides power output up to 5 amps (100 watts), which is sufficient for fast-charging, syncing and powering most large-capacity devices.

Reversible Thunderbolt 3 Connectors Attach in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible Thunderbolt 3 male connectors plug into a Thunderbolt 3 or USB-C port in either direction for a fumble-free connection every time. Note: both ends must be connected to a Thunderbolt 3 port to achieve 40 Gbps transfer speeds.

Specifications

Highlights

- Thunderbolt 3 cable is compatible with all USB-C and Thunderbolt 3 devices
- Supports Thunderbolt 3 speeds up to 40 Gbps—4x faster than USB 3.1 Gen 2
- Provides 5A (100W) power output for charging and powering large-capacity mobile devices
- Reversible Thunderbolt 3 plugs connect in either direction for immediate no-fuss use
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Connect your laptop to a docking station or hub with a USB-C or Thunderbolt 3 port
- Bridge two Thunderbolt 3-enabled notebooks for migrating data or setting up a peer-to-peer network
- Stream 4K video from your MacBook or Chromebook to a monitor or television with a Thunderbolt 3-enabled input
- Connect a DisplayPort monitor or laptop to an external GPU box for playing graphics-intensive 4K video games

System Requirements

- Devices with Thunderbolt 3 or USB-C ports (40 Gbps speeds possible only through Thunderbolt 3)

Package Includes

- MTB3-02M-5A-AB Thunderbolt 3 Cable, M/M, 2 m, Black



Powering Business Worldwide

TRIPP LITE
SERIES

UPC Code	037332242013
Technology	Thunderbolt
POWER	
Power Consumption (Watts)	1.5
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	2.0
CONNECTIONS	
Side A - Connector 1	THUNDERBOLT 3 (Type-C MALE)
Side B - Connector 1	THUNDERBOLT 3 (Type-C MALE)
Connector Plating	Nickel
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Outer Diameter (OD)	+/- 4.75 mm
Cable Length (ft.)	6.6
Cable Length (m)	2.01
Cable Length (in.)	78.74
Cable Length (cm)	200
ENVIRONMENTAL	
Operating Temperature Range	32° to 122°F (0° to 50°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	25% ~ 85% RH
Power Provided to Connected Device(s)	5A (100W) Power Delivery
FEATURES & SPECIFICATIONS	
Data Transfer Rate	40 Gbps
High Voltage	No
Locking Plug	No
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)



Powering Business Worldwide

TRIPP LITE
SERIES

WARRANTY & SUPPORT

Product Warranty Period (Worldwide)	3-year limited warranty
--	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[MTB3-02M-5A-AB](#)