

# 12-Port Wall-Mount Patch Panel for UTP Keystone Jacks, Offset Ports, TAA

MODEL NUMBER: N062-012-KJ-WOF



Manages and organizes input/output network cable connections in your small network closet, including audio/video, VoIP, Ethernet and USB.

## Features

### Manages and Organizes up to 12 Cable Connections

This 12-port patch panel is ideal for wall mounting in small network closets or near a desk or workspace. Twelve blank offset cutouts accommodate almost any standard keystone jack, including RJ45 Ethernet, HDMI and USB. Ports are numbered and labeled to help you identify individual cable runs at a glance.

### Designed for Easy Custom Installation

The 12-port patch panel mounts to a wall, desk or similar flat surface in either horizontal or vertical mode, so you can easily organize inputs to your specific requirements. It easily snaps into and out of the frame, allowing you to remove it to make new connections and snap it back into place.

### TAA-Compliant for GSA Schedule Purchases

The N062-012-KJ-WOF is compliant with the Federal Trade Agreements Act (TAA), which makes it eligible for GSA (General Services Administration) Schedule and other federal procurement contracts.

## Highlights

- 12 blank cutouts accommodate all UTP keystone jacks, including RJ45, HDMI and USB
- Installs on a wall vertically or horizontally with included mounting bracket
- Ports are numbered and labeled for at-a-glance connection identification
- Recommended for AV, VoIP, Ethernet and other applications in small network closets
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Package Includes

- N062-012-KJ-WOF 12-Port Wall-Mount Patch Panel
- Mounting bracket
- Installation instructions

## Specifications

| OVERVIEW             |   |
|----------------------|---|
| UPC Code             | 037332285140  |
| Product Type         | Wall Mount  |
| Technology           | Cat5/5e; Cat6; Cat6a  |
| CONNECTIONS          |   |
| Number of Ports      | 12  |
| Ports Detail         | 12 DEDICATED PORTS AVAILABLE FOR MOUNTING STANDARD KEYSTONE JACKS |
| Side A - Connector 1 | KEYSTONE JACK CUTOUT  |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |   |
|--------------------------------------|---|
| Side B - Connector 1                 | KEYSTONE JACK CUTOUT                    |
| <b>PHYSICAL</b>                      |   |
| Color                                | Black                                   |
| Material of Construction             | PANEL: SECC; WM BRACKET: ABS (UL94V-0)  |
| Mounting Holes or Slots              | Yes                                     |
| Total Number of Ports                | 12                                      |
| Rackmountable                        | No                                      |
| Shipping Dimensions (hwd / in.)      | 3.03 x 11.18 x 3.11                     |
| Shipping Weight (lbs.)               | 0.66                                    |
| Shipping Weight (kg)                 | 0.30                                    |
| Unit Dimensions (hwd / in.)          | 9.960 x 2.550 x 2.750                   |
| Housing                              | SECC                                    |
| Mounting Details                     | WALL MOUNT                              |
| Panel Style                          | Blank                                   |
| <b>ENVIRONMENTAL</b>                 |   |
| Operating Temperature Range          | 14° to 140°F (-10° to 60°C)             |
| Storage Temperature Range            | -40° to 158°F (-40° to 70°C)            |
| Operating Humidity Range             | 10% TO 90% RH, NON-CONDENSING           |
| Storage Humidity Range               | 10% TO 90% RH, NON-CONDENSING           |
| <b>FEATURES &amp; SPECIFICATIONS</b> |   |
| Mounting Accessory Included          | Yes                                     |
| Breakout                             | No                                      |
| Numbered Ports                       | Yes                                     |
| Driver Required                      | No                                      |
| DIN Mountable                        | No                                      |
| Keystone Jacks                       | Yes                                     |
| Labeled Ports                        | No                                      |
| Panel Applications                   | Audio/Video; Ethernet; USB              |
| <b>STANDARDS &amp; COMPLIANCE</b>    |   |
| Product Certifications               | UL 94                                   |
| Product Compliance                   | REACH; RoHS; Trade Agreements Act (TAA) |
| <b>WARRANTY &amp; SUPPORT</b>        |   |



Powering Business Worldwide

TRIPP LITE  
SERIES

|  |                           |
|--|---------------------------|
| Product Warranty Period<br>(Worldwide) | Lifetime limited warranty |
|--|---------------------------|

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[N062-012-KJ-WOF](#)