

16-Port Fiber Patch Panel, 1U (ST/ST), Multimode or Singlemode

MODEL NUMBER: **N490-016-STST**



Highlights

- Simplified Fiber Optic Patching
- Multimode 62.5/125 or 50/125, Singlemode 9/125
- 16 ports in 1U of rackspace

Package Includes

- 16 Port ST/ST Duplex Multimode or Singlemode Fiber Optic Patch Panel

Description

This 16-port 1U rack-mount ST/ST Fiber Optic Patch Panel provides efficient and easy management of fiber optic cables in the rack or cabinet. Pre-loaded, feed-through duplex multimode connectors are mounted on a 16-gauge, cold-rolled, black powder-coated steel panel. Use with 62.5/125 or 50/125 Multimode or 9/125 Singlemode fiber Ethernet cables. Panel measures 19 inches wide by 1.75 inches high.

Features

- 16 ports ST/ST
- Only 1U of rack-space
- Use with 62.5/125 or 50/125 Multimode, or 9/125 Singlemode fiber patch cables
- Available in ST/ST, SC/SC, LC/LC,

Specifications

OVERVIEW	
UPC Code	037332135346
Product Type	Feed-Through
Technology	Multimode
CONNECTIONS	
Number of Ports	16
Side A - Connector 1	ST DUPLEX (FEMALE)
Side B - Connector 1	ST DUPLEX (FEMALE)
PHYSICAL	

Shipping Dimensions (hwd / in.)	3.90 x 3.10 x 21.80
Shipping Dimensions (hwd / cm)	9.91 x 7.87 x 55.37
Shipping Weight (lbs.)	1.00
Shipping Weight (kg)	0.45
Panel Style	Pass-Through
COMMUNICATIONS	
Insertion Loss	0.1 dB
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[N490-016-STST](#)