

Important Note

This product is not available in the European Union. If you live in one of these countries, please contact us for further assistance.

Hospital-Grade Power Cord, NEMA 5-15P to Locking IEC C13 - Green Dot, 10A, 125V, 18 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: P006-L10-HG10



Connects a PC, printer, monitor, scanner or other hospital equipment with a C14 inlet to a grounded hospital-grade AC outlet.

Features

Hospital-Grade Power Cable is a Safe Solution for Medical Facilities This hospital-grade IEC power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible equipment with a three-pin C14 inlet in a hospital or other medical facility. It features a locking C13 end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source located outside patient care vicinities. The 10-ft. (3.05 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Locking C13 Connector Helps Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking C13 connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Lifetime Warranty The P006-L10-HG10 is backed by a lifetime warranty, ensuring reliability and performance.

Specifications

OVERVIEW	
UPC Code	037332224705
Device Compatibility	Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU

Highlights

- Recommended for connecting devices to power outlets outside patient care vicinities
- 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet
- Hospital-grade power cable replaces or upgrades power cord provided by manufacturer
- NEMA 5-15P-HG plug connects to AC power; C13 plug connects to device's C14 inlet
- Locking C13 connector maintains secure link to avoid loss of power and costly downtime

Applications

- Connect a mobile cart battery, monitor, computer or printer to a hospital-grade surge protector up to 10-ft. (3.05 m) away in a hospital environment outside patient care vicinities
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P006-L10-HG10 Hospital-Grade Power Cord, NEMA 5-15P to Locking IEC C13, 10-ft. (3.05 m), Black



Powering Business Worldwide

TRIPP LITE
SERIES

Country/Region	North America
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P-HG
Side B - Connector 1	IEC-320-C13 - LOCKING
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	10
Cable Length (m)	3.05
Shipping Dimensions (hwd / in.)	12.80 x 8.86 x 0.50
Shipping Dimensions (hwd / cm)	32.51 x 22.50 x 1.27
Shipping Weight (lbs.)	0.80
Shipping Weight (kg)	0.36
ENVIRONMENTAL	
Operating Temperature Range	-4° to 221°F (-20° to 105°C)
Storage Temperature Range	-4° to 221°F (-20° to 105°C)
Operating Humidity Range	0% to 65% RH
Storage Humidity Range	0% to 65% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P006-L10-HG10](#)