

## 3-Slot Power Cord, NEMA 5-15P to C5 - Laptop/Notebook, 10A, 125V, 18 AWG, 3 ft. (0.91 m), Black

MODEL NUMBER: P013-003



Laptop power cord connects your notebook or laptop with a 3-slot C6 power inlet to an AC outlet.

### Features

**Laptop Power Cable Connects Notebook Computers to an AC Outlet** This NEMA 5-15P to C5 power cord is designed for connecting a notebook computer, laptop or other device with a three-slot C6 inlet to an AC wall outlet, surge protector, UPS system or PDU. It also powers some portable projectors, desktop computers and LG LCD televisions. The three-foot length helps reduce cable clutter and minimize the risk of tripping.

### Highlights

- Recommended for powering notebook computers and laptops with C6 inlets
- 3-ft. (0.91 m) length allows flexibility in placing devices, while avoiding cable clutter
- Ideal replacement for a worn-out or missing laptop power cable

### Applications

- Connect a laptop or notebook computer to a surge protector up to 3 ft. away in your workstation
- Extend an existing power connection up to 3 ft. to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing laptop power cord

### Package Includes

- P013-003 3-Slot Power Cord, NEMA 5-15P to C5 - 6 ft., Black

## Specifications

| OVERVIEW                    |   |
|-----------------------------|---|
| UPC Code                    | 037332185907  |
| Device Compatibility        | Laptop; Computer; Projector; Monitor/HDTV; UPS; PDU |
| Country/Region              | North America                                       |
| INPUT                       |   |
| Maximum Input Amps          | 10  |
| Voltage Compatibility (VAC) | 125   |
| CONNECTIONS                 |   |
| Side A - Connector 1        | NEMA 5-15P  |
| Side B - Connector 1        | IEC-320-C5  |
| PHYSICAL                    |   |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                             |
|--------------------------------------|-----------------------------|
| Plug Color                           | Black                       |
| Cable Jacket Color                   | Black                       |
| Cable Jacket Material                | PVC                         |
| Cable Jacket Rating                  | VW-1                        |
| Power Cord Jacket Type               | SVT                         |
| Cable Outer Diameter (OD)            | 6.3mm                       |
| Number of Conductors                 | 3                           |
| Wire Gauge (AWG)                     | 18                          |
| Wire Gauge (OD - mm <sup>2</sup> )   | 0.82                        |
| Cable Length (ft.)                   | 3                           |
| Cable Length (m)                     | 0.91                        |
| Shipping Dimensions (hwd / in.)      | 8.86 x 12.80 x 0.50         |
| Shipping Dimensions (hwd / cm)       | 22.50 x 32.51 x 1.27        |
| Shipping Weight (lbs.)               | 0.24                        |
| Shipping Weight (kg)                 | 0.11                        |
| <b>ENVIRONMENTAL</b>                 |                             |
| Operating Temperature Range          | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range            | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range             | 10% to 65% RH               |
| Storage Humidity Range               | 10% to 65% RH               |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                             |
| Antibacterial                        | No                          |
| Angled Plug                          | No                          |
| High Voltage                         | No                          |
| Locking Plug                         | No                          |
| Coiled Power Cord                    | No                          |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                             |
| Product Certifications               | cUL Listed; UL Listed       |
| Product Compliance                   | RoHS                        |
| <b>WARRANTY &amp; SUPPORT</b>        |                             |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty   |



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P013-003](#)