

# High-Speed HDMI Flat Cable, Digital Video with Audio, UHD 4K (M/M), Black, 16 ft. (4.88 m)

MODEL NUMBER: P568-016-FL



## Highlights

- Premium double-shielded digital audio/video cable
- Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter
- Gold-plated connectors provide optimal signal transfer
- High Speed HDMI and HDCP compliant
- Supports Ultra High Definition (UHD) 4K video resolutions

## Package Includes

- 16-ft. Flat High Speed HDMI Gold Cable

## Features

- Flat design for better manageability
- Flat conductors reduce crosstalk and inductance
- Creates a pure digital connection between HDMI-enabled HDTV display devices and HDMI-enabled digital video sources
- Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter
- Gold-plated connectors provide optimal signal transfer
- Premium double-shielded cable protects against outside noise (EMI/RFI)
- Impedance-matched twisted-pair construction reduces cross-talk and interference
- Perfect for connecting an iPad2 to an HDTV (video mirroring) to watch movies, play games, surf the web and display presentations
- Supports Ultra High Definition (UHD) 4K video resolutions

## Specifications

| OVERVIEW                       |                         |
|--------------------------------|-------------------------|
| UPC Code                       | 037332137913            |
| Product Type                   | Passive Cable           |
| Technology                     | HDMI                    |
| Cable Type                     | Passive                 |
| VIDEO                          |                         |
| Max Supported Video Resolution | 3840 x 2160 (4K) @ 30Hz |
| Max Supported Color Depth      | 24-bit True Color       |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                              |                      |
|----------------------------------------------|----------------------|
| HDR Support                                  | No                   |
| 3D Video Supported                           | No                   |
| Chroma Sub Sampling                          | 4:4:4                |
| EDID Support                                 | Yes                  |
| Signal Transmission                          | Bidirectional        |
| <b>AUDIO</b>                                 |                      |
| Audio Specification                          | Stereo Audio         |
| <b>CONNECTIONS</b>                           |                      |
| Side A - Connector 1                         | HDMI (MALE)          |
| Side B - Connector 1                         | HDMI (MALE)          |
| Connector Plating                            | Gold                 |
| Contact Plating                              | Gold                 |
| Connector Style                              | Straight             |
| Latching or Gripping Connector               | No                   |
| <b>USER INTERFACE, ALERTS &amp; CONTROLS</b> |                      |
| LED Indicators                               | 0                    |
| <b>PHYSICAL</b>                              |                      |
| Color                                        | Black                |
| Cable Jacket Color                           | Black                |
| Connector Color                              | Black                |
| Cable Jacket Material                        | PVC                  |
| Cable Jacket Rating                          | VW-1                 |
| Cable Outer Diameter (OD)                    | 3.0*12.0mm           |
| Wire Gauge (AWG)                             | 30                   |
| Cable Length (ft.)                           | 16                   |
| Cable Length (m)                             | 4.88                 |
| Cable Length (in.)                           | 192                  |
| Ferrite Core                                 | No                   |
| Minimum Bend Radius                          | 30mm                 |
| Shipping Dimensions (hwd / in.)              | 11.00 x 7.00 x 0.50  |
| Shipping Dimensions (hwd / cm)               | 27.94 x 17.78 x 1.27 |
| Shipping Weight (lbs.)                       | 0.90                 |
| Shipping Weight (kg)                         | 0.41                 |



Powering Business Worldwide

TRIPP LITE  
SERIES

| ENVIRONMENTAL                                |                               |
|----------------------------------------------|-------------------------------|
| Operating Temperature Range                  | 32° to 113°F (0° to 45°C)     |
| Storage Temperature Range                    | -40° to 176°F (-40° to 80°C)  |
| Operating Humidity Range                     | 10% to 85% RH, Non-Condensing |
| Storage Humidity Range                       | 5% to 90% RH, Non-Condensing  |
| COMMUNICATIONS                               |                               |
| Consumer Electronics Control (CEC) Supported | Yes                           |
| FEATURES & SPECIFICATIONS                    |                               |
| EMI/RFI Line Noise Protection                | No                            |
| MST Support                                  | No                            |
| Antibacterial                                | No                            |
| IP68 Rated                                   | No                            |
| IP20 Rated                                   | No                            |
| Armored Cable                                | No                            |
| Ethernet Support                             | No                            |
| HDCP Specification                           | 1.3                           |
| STANDARDS & COMPLIANCE                       |                               |
| Product Compliance                           | RoHS; REACH                   |
| WARRANTY & SUPPORT                           |                               |
| Product Warranty Period (Worldwide)          | Lifetime limited warranty     |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[P568-016-FL](#)