

SmartRack 12-in. (30.48 cm) Width High Capacity Vertical Cable Manager - Double finger duct with cover

MODEL NUMBER: SRCABLEVRT12



Highlights

- Vertical Cable Manager, 6-ft. (1.83 m), finger duct with cover
- High capacity (12-in. (30.48 cm) width) for large cable bundles
- Split into three 2-ft. (0.61 m) sections to allow for multiple installation options
- Helps eliminate cable stress
- Organizes cables within an Open Rack
- Toolless button mounts
- Cold rolled steel with black finish

Package Includes

- Vertical Cable Manager, 6-ft. (1.83 m), finger duct with cover, mounting hardware

Description

The SmartRack® SRCABLEVRT12 helps eliminate cable stress by organizing the cables within an open rack cabinet. The vertical cable manager (finger duct with cover) is six feet (1.8 meters) high, 12 inches (30.5 centimeters) wide and split into three two-foot (0.6-meter) sections to allow for multiple installation options. SRCABLEVRT12 offers toolless button mounting.

Features

- SmartRack SRCABLEVRT12 helps eliminate cable stress by organizing the cables within an Open Rack cabinet
- The vertical cable manager (finger duct with cover) is 6-ft. (1.83 m) high, 12 inch (30.48 cm) width and split into three 2-ft (0.61 m) sections to allow for multiple installation options
- Toolless button mounting

Specifications

| OVERVIEW | |
|---------------------------------|------------------------------|
| UPC Code | 037332161284 |
| Accessory Type | Cable Management Accessories |
| PHYSICAL | |
| Color | Black |
| Shipping Dimensions (hwd / in.) | 4.80 x 25.10 x 26.00 |
| Shipping Dimensions (hwd / cm) | 12.19 x 63.75 x 66.04 |
| Shipping Weight (lbs.) | 31.30 |
| Shipping Weight (kg) | 14.20 |

| | |
|-------------------------------------|-------------------------|
| Unit Dimensions (hwd / in.) | 24.450 x 12.900 x 6.020 |
| Unit Dimensions (hwd / cm) | 62.10 x 32.77 x 15.29 |
| Unit Weight (lbs.) | 9.2 |
| Unit Weight (kg) | 4.17 |
| Cable Manager Form Factor | Vertical |
| FEATURES & SPECIFICATIONS | |
| IP68 Rated | No |
| IP20 Rated | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS; EIA/ECA-310-E |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 5-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[SRCABLEVRT12](#)