

USB 2.0 Panel Mount Extension Cable (A M/F), 6-in. (15.24 cm)

MODEL NUMBER: **U024-06N-PM**



Description

This 6-in. (15.24 cm) Panel Mount USB extension cable is manufactured using USB2.0 cable. It features a panel mount connector that allows you to secure a USB A female port in a fixed location, such as a motherboard, podium, or kiosk. It is designed for use with USB 2.0 device cables, but is backwards compatible and can also be used with USB 1.1 cables. Made with superior foil shielding for reliable error-free data communications. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

Features

- Secure a USB A female port in a fixed location, such as a motherboard, podium, or kiosk
- Extend distances of USB 2.0 cables with this extension cable
- Data transfer rates (1.5 to 480 Mbps) for low speed and high speed devices
- Premium double-shielded cables with aluminum braid and aluminum Mylar foil feature twisted 28/20 AWG data lines

Highlights

- Secure a USB A female port in a fixed location, such as a motherboard, podium, or kiosk
- Extend distances of USB 2.0 cables with this extension cable
- Data transfer rates (1.5 to 480 Mbps) for low speed and high speed devices
- Premium double-shielded cables with aluminum braid and aluminum mylar foil feature twisted 28/20 AWG data lines

System Requirements

- Any device requiring a longer USB cable

Package Includes

- U024-06N-PM 6 in. Panel Mount USB 2.0 Extension Cable (USB A M/F)

Specifications

OVERVIEW	
UPC Code	037332178459
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB A (FEMALE) - PANEL MOUNT
Connector Style	Straight



Powering Business Worldwide



PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.07
Shipping Weight (kg)	0.03
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 89% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U024-06N-PM](#)