

USB-A to USB-C Cable, USB 2.0, (M/M), 3 ft. (0.91 m)

MODEL NUMBER: **U038-003**



Connect devices with a USB Type-C (USB-C) connector to a USB Charger, or the USB port on your laptop, ultrabook or computer

Description

This U038-003 USB 2.0 A to USB Type-C (USB-C) device cable connects devices with a USB Type-C connector to a USB charger or the USB port on your laptop, Ultrabook or PC. The USB Type-C connector is reversible, so there is no guessing on which way to plug it in...it connects in either direction! Backward compatible - can be used with older USB 1.1 applications as well. USB 2.0 cabling includes superior foil shielding for reliable, error-free data communications. Features nickel-plated connectors and gold-plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life.

Features

- 3-ft. (0.91 m) USB 2.0 A to USB Type-C (USB-C) device cable
- Connect devices with a USB Type-C connector to a USB Charger, or the USB port on your laptop, ultrabook, or computer
- USB Type-C connector is reversible, so there is no guessing on which way to plug it in.....it connects in either direction!
- Supports USB 2.0 data transfer rates up to 480Mbps
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 30AWG Data Pair / 24AWG Power pair

Specifications

OVERVIEW	
UPC Code	037332188564
Technology	USB 2.0 (High Speed)
Cable Type	Passive

Highlights

- 3-ft. (0.91 m) USB 2.0 A to USB Type-C (USB-C) device cable
- USB Type-C connector is reversible, so there is no guessing on which way to plug it in

System Requirements

- A device with a USB Type-C (USB-C) connector
- A USB charger, or a laptop, ultrabook or computer with an available USB A port

Package Includes

- USB 2.0 A Male to USB Type-C (USB-C) Male Device Cable - 3-ft. (0.91 m)



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.0MM
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.08
Shipping Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10% to 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U038-003](#)