

## USB-A to USB-C Cable, USB 2.0, (M/M), 6 ft. (1.83 m)

MODEL NUMBER: **U038-006**



Connect devices with a USB Type-C (USB-C) connector to a USB charger, or the USB port on your laptop, ultrabook or computer

### Features

- 6-ft. USB 2.0 A to USB Type-C (USB-C) device cable
- Connect devices with a USB Type-C connector to a USB charger, or the USB port on your laptop, ultrabook or computer
- USB Type-C connector is reversible, so there is no guessing on which way to plug it in.....it connects in either direction!
- Supports USB 2.0 data transfer rates up to 480Mbps
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 28AWG Data Pair / 22AWG Power pair

## Specifications

| OVERVIEW             |                      |
|----------------------|----------------------|
| UPC Code             | 037332188571         |
| Technology           | USB 2.0 (High Speed) |
| Cable Type           | Passive              |
| CONNECTIONS          |                      |
| Side A - Connector 1 | USB A (MALE)         |
| Side B - Connector 1 | USB C (MALE)         |
| Connector Plating    | Nickel               |
| Contact Plating      | Gold                 |

### Highlights

- 6-ft. USB 2.0 A to USB Type-C (USB-C) device cable
- USB Type-C connector is reversible, so there is no guessing on which way to plug it in

### System Requirements

- A device with a USB Type-C (USB-C) connector
- A USB charger, or a laptop, ultrabook or computer with an available USB A port

### Package Includes

- USB 2.0 A Male to USB Type-C (USB-C) Male Device Cable - 6-ft



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| Connector Style                      | Straight                            |
| <b>PHYSICAL</b>                      |                                     |
| Material of Construction             | PVC                                 |
| Cable Jacket Color                   | Black                               |
| Cable Jacket Rating                  | VW-1                                |
| Cable Outer Diameter (OD)            | 3.5MM                               |
| Cable Length (ft.)                   | 6                                   |
| Cable Length (m)                     | 1.83                                |
| Cable Length (in.)                   | 72                                  |
| Shipping Dimensions (hwd / in.)      | 9.00 x 7.00 x 0.50                  |
| Shipping Dimensions (hwd / cm)       | 22.86 x 17.78 x 1.27                |
| Shipping Weight (lbs.)               | 0.09                                |
| Shipping Weight (kg)                 | 0.04                                |
| <b>ENVIRONMENTAL</b>                 |                                     |
| Operating Temperature Range          | 14° to 140°F (-10° to 60°C)         |
| Storage Temperature Range            | -4° to 185°F (-20° to 85°C)         |
| Relative Humidity                    | 10% to 85%, Non-Condensing          |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                                     |
| USB Specification                    | USB 2.0 (up to 480 Mbps)            |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                                     |
| Product Compliance                   | RoHS; CE (Europe); REACH; FCC (USA) |
| <b>WARRANTY &amp; SUPPORT</b>        |                                     |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty           |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U038-006](#)