

4-Port USB 2.0 over Cat5 Hub with 4 Remote Ports, TAA

MODEL NUMBER: U224-4R4-R



Highlights

- Locate 4 USB 1.1 peripherals up to 150-ft. (45.72 m) from your computer
- Uses readily available Cat5e/Cat6 patch cable
- Plug-and-play; no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Local transmitter unit
- 4-Port remote receiver unit
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 4.5 ft.)
- Owner's manual

Description

4-Port USB 1.1 over Cat5 extender hub allows USB peripherals to be located up to 150 feet (45.7 meters) from your computer. Simply plug the transmitter into the USB port on your computer, connect your USB peripherals and run Cat5e/Cat6 cable up to 150 feet to the remote receiver unit and connected devices. Plug-and-play; no software or drivers required. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Locate 4 USB 1.1 peripherals up to 150-ft. (45.72 m) from your computer
- Uses readily available Cat5e/Cat6 patch cable
- Plug-and-play; no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332146687
Product Type	Hub
Technology	USB 2.0 (High Speed)
Host Connector	USB A (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

DATA	
Data Ports	(4) USB A (FEMALE)
Data Ports Details	(4) USB-A - USB 2.0
INPUT	
AC Power Adapter Plug(s)	NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.35A
AC Power Adapter Output Specs (V / A)	5V / 2A
AC Power Adapter Cord Length (ft.)	4.5
AC Power Adapter Cord Length (m)	1.5
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
POWER	
Power Source Type	AC Adapter
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 4.5 ft.
DC Barrel Plug	OD: 3.5 x 1.35 x 8mm, Positive Pin, Negative Sleeve
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB A (MALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	(4) USB A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Red - Connection; Green - Activity
PHYSICAL	
Color	Black
Material of Construction	Plastic
Receiver Unit Height (in.)	0.9
Receiver Unit Width (in.)	2.4
Receiver Unit Depth (in.)	3.3
Shipping Dimensions (hwd / in.)	2.30 x 8.90 x 5.90
Shipping Dimensions (hwd / cm)	5.84 x 22.61 x 14.99
Shipping Weight (lbs.)	0.75

Shipping Weight (kg)	0.34
Transmitter Unit Depth (in.)	2.6
Transmitter Unit Height (in.)	0.9
Transmitter Unit Width (in.)	1.8
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	4
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
External Power Supply Certifications	CE; FCC; UL
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U224-4R4-R](#)