

Important Note

Male-to-male is not a standard USB cable configuration. It's used only in rare instances where a peripheral or patch bay employs a female connector instead of a USB-B port. Not for use with U325-000-KP-BK, U325-000-KPA-BK or U325-001-KPA-BK. The U325-003 and U325-006 USB A Male/Male cables are designed for use with those products. This cable will not connect two PCs. File-sharing between computers requires special software-driven cables, such as U234-006-MP-R.

USB 3.0 SuperSpeed A/A Cable (M/M), Black, 6 ft. (1.83 m)

MODEL NUMBER: **U320-006-BK**



Connects peripherals and patch bays with female USB-A ports to your computer, laptop or other compatible USB 3.0 device, such as a Chromebook™ or Microsoft® Surface®.

Features

Connects Your USB Type-A Peripherals to Your Computer

- Recommended for peripherals, patch bays, computers, laptops and other compatible USB 3.0 devices with female connectors
- Supports data transfer rates up to 5 Gbps
- Bi-directional data interface allows data to flow both directions
- Backward compatible with earlier USB generations

First-Rate Construction for Superior Signal Transfer

- Premium foil and braid shielding for EMI/RFI noise protection
- Molded nickel-plated connectors for optimal signal quality
- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Flexible PVC jacket easy to install in tight spaces

Specifications

Highlights

- Supports data transfer rates up to 5 Gbps
- Nickel-plated connectors with gold-plated contacts
- Data flows both directions simultaneously
- Twisted 28/24 AWG data/power lines
- Backward compatible with earlier USB generations

System Requirements

- Computer with USB-A female port
- Peripheral or patch bay with USB-A female port

Package Includes

- U320-006-BK USB 3.0 SuperSpeed A/A Cable (M/M)



Powering Business Worldwide

TRIPP LITE
SERIES

UPC Code	037332198730
Technology	USB 3.x
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (MALE)
Connector Style	Straight
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.50
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 24.13
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U320-006-BK](#)