

## 4-Port Portable USB 3.x (5Gbps) Hub

MODEL NUMBER: U360-004-MINI



Connect up to four USB devices via a single USB 3.0 port on your desktop, laptop, or tablet

### Description

The U360-004-MINI is a compact 4-port USB 3.2 hub with built-in cable that provides up to 5 Gbps transfer rates in a compact, portable format (computer and devices must be both USB 3.2 rated to achieve maximum 5 Gbps speeds). Hub is backward compatible to USB 2.0 and 1.1, so that older USB devices can be attached (devices will run at their native speeds of 480 Mbps and 12 Mbps respectively ). Small, portable design allows the hub to travel easily, and built-in cable eliminates the need to carry a separate cable for attachment to laptops and tablets. Needed power comes from the attached computer. No need for external power adapter. Plug-n-Play...no drivers or software required. Works with all Windows and macOS operating systems.

### Features

- Add 4 additional USB 3.0 ports to your PC, Laptop, or Tablet
- Compact design...4in long by 1.25in wide by .75in high
- Built-in 1-ft. attachment cable
- USB 3.0 SuperSpeed 5gbps
- Plug-n-Play...no drivers or software to load
- Bus powered...separate power supplied not needed
- Compatible with all Windows and MAC OS
- Backward compatible with Hi-Speed ( 480Mbps ), Full Speed ( 12Mbps ), and Low Speed ( 1.5Mbps ) USB versions

### Highlights

- Portable design with built-in 1-ft. cable
- USB data transfer rates up to 5Gbps
- Plug and Play

### System Requirements

- Desktop, Laptop or Tablet with USB 3.0 USB port
- USB 3.0 ( or less ) Peripherals

### Package Includes

- Portable USB 3.0 SuperSpeed Hub - 4-Port

## Specifications

OVERVIEW	
UPC Code	037332184726
Product Type	Hub
Technology	USB 3.x
Host Connector	USB A (MALE)



Powering Business Worldwide

**TRIPP-LITE**  
by **EAT•N**

VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DATA	
Data Ports	(4) USB A (FEMALE)
Data Ports Details	(4) USB-A - USB 3.2 Gen 1 (5 Gbps)
INPUT	
Bus Powered	Yes
Product Length (in.)	16.8
Product Length (cm.)	42.67
Product Length (ft.)	1.4
Product Length (m)	0.426
POWER	
Power Source Type	USB
Power Consumption (Watts)	0.77
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	(4) USB 3.0 A (FEMALE)
Connector Plating	Nickel
PHYSICAL	
Color	Black; Silver
Material of Construction	Plastic
Cable Jacket Rating	VW-1
Included Mounting Accessories	No
Shipping Dimensions (hwd / in.)	5.50 x 3.90 x 1.20
Shipping Dimensions (hwd / cm)	13.97 x 9.91 x 3.05
Shipping Weight (lbs.)	0.24
Shipping Weight (kg)	0.11
Unit Dimensions (hwd / in.)	0.750 x 3.500 x 2.250
Unit Packaging Type	Box



Powering Business Worldwide



Unit Weight (lbs.)	0.13
Unit Weight (kg)	0.06
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 158°F (-20° to 70°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	20% to 80% RH, Non-Condensing
BTUs	2.6 BTU/Hr
Power Provided to Connected Device(s)	5V 0.9A (4.5W) Output per USB port
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Hub Ports	Yes
Number of USB Hub Ports	4
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U360-004-MINI](#)