

USB-C to USB Micro-B Cable (M/M) - USB 3.2, Gen 2 (10 Gbps), Thunderbolt 3 Compatible, 3 ft. (0.91 m)

MODEL NUMBER: **U426-003-G2**



Connects a computer, laptop, tablet or other device with a USB-C port to a device or peripheral with a USB 3.0 Micro-B port, such as a smartphone or external hard drive.

Features

Supports USB 3.1 Gen 2

- Recommended for smartphones, tablets, laptops, computers, external hard drives and other compatible devices
- Data transfer speeds up to 10 Gbps
- Power output up to 3A—perfect for fast charging of most mobile devices
- Same USB Micro-B male connector as USB 3.0 devices
- Backward compatible with previous USB generations

USB-C Male Connector

- Fumble-free reversible plug ensures fast, easy connection every time

Premium Construction for Superior Signal Transfer

- Foil and braid shielding for error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors and gold-plated contacts
- Integral strain relief for long life
- Rugged PVC jacket

Specifications

OVERVIEW	
UPC Code	037332197382
Technology	Thunderbolt; USB 3.x

Highlights

- USB 3.1 Gen 2 data transfer speeds up to 10 Gbps
- Power output up to 3A for fast-charging devices
- Reversible USB-C male connector for fast connection the first time
- Error-free signal quality and EMI/RFI protection
- Backward compatible with previous USB generations

System Requirements

- Device with a USB-C port
- Device with a USB 3.0 Micro-B port

Package Includes

- U426-003-G2 USB 3.1 Gen 2 (10 Gbps) Cable, USB-C to USB 3.0 Micro-B (M/M), 3 ft.



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB 3.0 MICRO-B (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	4.5MM
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	9.00 x 6.80 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.27 x 1.27
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10 to 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.1 Gen 2 (up to 10 Gbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U426-003-G2](#)