

4-Port USB-C Hub, USB 3.x (5Gbps), 4x USB-A Ports, Black

MODEL NUMBER: **U460-004-4AB**



USB 3.1 Type-C hub adds 4 USB-A ports to your laptop, MacBook, Chromebook or other compatible device.

Features

USB 3.1 Type-C Hub Connects to Your Device's USB-C or Thunderbolt 3 Port This USB-C hub expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive, external hard drive, digital camera, MP3 player and other USB peripherals.

Connects Up to 4 USB-A Peripherals Four USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer, and all four provide up to 1.5A for charging smartphones and other mobile devices. All ports support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices. **Note:** Host must support USB OTG (On-the-Go) **Built-In USB-C Cable Connects in Either Direction**

Connect the reversible USB-C plug to your source device's Thunderbolt 3 or USB Type-C connector. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

Ready to Use Right Out of the Package The plug-and-play USB 3.1 Type-C hub requires no software, drivers or external power. The lightweight case fits easily into a pocket, briefcase or laptop bag for connecting on the go.

3-Year Warranty and Environmentally Responsible Design The U460-004-4AB comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting commitment to environmental responsibility.

Specifications

OVERVIEW	
UPC Code	037332209580
Product Type	Hub

Highlights

- Supports USB 3.1 Gen 1 for fast data transfers up to 5 Gbps
- Accepts up to 4 USB peripherals, turning your laptop into a mini workstation
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- USB ports provide up to 5V/1.5A (7.5W) for charging smartphones and other devices
- Easy installation with plug-and-play operation—no software required

Applications

- Transfer files to and from a USB thumb drive or external hard drive
- Connect your smartphone or other mobile device to build up a full charge
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone

System Requirements

Tablet, laptop, Chromebook, MacBook, smartphone or PC with USB-C or Thunderbolt 3 port.

Package Includes

U460-004-4AB 4-Port USB 3.1 Hub, 4x USB-A, Thunderbolt - Black



Powering Business Worldwide

TRIPP LITE
SERIES

Technology	USB 3.x
Host Connector	USB C (MALE)
VIDEO	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
DisplayPort Alt Mode	No
DATA	
Data Ports	(4) USB A (FEMALE)
Data Ports Details	(4) USB-A - USB 3.2 Gen 1 (5 Gbps)
INPUT	
Built-In Cable Length (ft.)	0.656
Built-In Cable Length (m)	0.2
Built-In Cable Length (in.)	7.87
Built-In Cable Length (cm)	20
Bus Powered	Yes
Product Length (in.)	11.7
Product Length (cm.)	29.72
Product Length (ft.)	0.98
Product Length (m)	0.3
BATTERY	
Battery Charging (5V/1.5A Port)	Yes
POWER	
Power Consumption (Watts)	0.7
CONNECTIONS	
Number of Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(4) USB 3.0 A (FEMALE)
Connector Plating	Nickel
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	White (Connection to Power)



Powering Business Worldwide

TRIPP LITE
SERIES

CHARGING	
Total Charging Watts	7.5
Charging Ports	USB-A: 5V 1.5A (7.5W)
Charging Ports / Amps	(4) 1.5A
PHYSICAL	
Color	Black
Material of Construction	Plastic
Cable Jacket Rating	VW-1
Shipping Dimensions (hwd / in.)	1.06 x 3.00 x 5.70
Shipping Weight (lbs.)	0.20
Unit Dimensions (hwd / in.)	0.840 x 3.800 x 1.200
Unit Dimensions (hwd / cm)	2.14 x 9.65 x 3.05
Unit Packaging Type	Box
Unit Weight (lbs.)	0.09
Unit Weight (kg)	0.04
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Relative Humidity	20% to 80% RH, Non-Condensing
BTUs	2.4 BTU/Hr
Power Provided to Connected Device(s)	Up to 5V 1.5A (7.5W) per USB Port
FEATURES & SPECIFICATIONS	
USB Hub Ports	Yes
Number of USB Hub Ports	4
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)
UASP Support	No
Auto MDIX Support	No
Full Duplex Support	No
Suspend Mode Support	No
Remote Wakeup Support	No
Driver Required	No
STANDARDS & COMPLIANCE	



Powering Business Worldwide

TRIPP LITE
SERIES

TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U460-004-4AB](#)