

HC2

High Power Resonant Capacitors



FEATURES

High AC Voltage - High Current

APPLICATIONS

Induction Heating, Tank Circuits

KVAR	200
CAPACITANCE TOLERANCE	+/-10%
MAXIMUM CORE TEMPERATURE	+85°C
SURFACE TEMPERATURE	+45°C (Above 45°C the KVAR rating must be de-rated by 2.25%/°C)
CONSTRUCTION	Self-healing
SELF INDUCTANCE	< 3 nH
DIELECTRIC	Polypropylene
FLAME RETARDANT	UL94V0

Standard Part Listing

Capacitance (μF)	VAC	IC part number	Maximum RMS current (A)	MAX power KVAR	Frequency range (kHz)	ESR (mΩ) 100kHz, +25°C	Dimensions (mm)			Terminal Style
							B	H	L	
0.05	1000	503HC2102K2CM6	250	200	636-994	1.5	30.2	30	68	2CM6
		503HC2102K2SM6								2SM6
0.1	1000	104HC2102K2CM6	250	200	318-498	1.2	30.2	30	68	2CM6
		104HC2102K2SM6								2SM6
0.17	900	174HC2900K2CM6	300	200	232-422	1	30.2	30	68	2CM6
		174HC2900K2SM6								2SM6
0.25	800	254HC2800K2CM6	300	200	199-286	0.9	30.2	30	68	2CM6
		254HC2800K2SM6								2SM6
0.33	800	334HC2800K2CM6	300	200	150-216	0.8	30.2	30	68	2CM6
		334HC2800K2SM6								2SM6
0.5	800	504HC2800K2CM6	350	200	98-194	0.6	30.2	30	68	2CM6
		504HC2800K2SM6								2SM6
0.66	700	664HC2700K2CM6	400	200	98-193	0.4	30.2	30	68	2CM6
		664HC2700K2SM6								2SM6
1.2	600	125HC2600K2CM6	450	200	74-134	0.4	30.2	30	68	2CM6
		125HC2600K2SM6								2SM6
1.33	600	135HC2600K2CM6	450	200	65-120	0.4	30.2	30	68	2CM6
		135HC2600K2SM6								2SM6
2.4	450	245HC2450K2CM6	500	200	65-85	0.3	30.2	30	68	2CM6
		245HC2450K2SM6								2SM6

Americas / EU

Phone: 1-508-996-8561

Email: cdena@cde.com



**CORNELL
DUBILIER**



Asia

Phone: 852-2793-0931


Email: cdeasia@cde.com

HC2

High Power Resonant Capacitors




TERMINAL STYLE: 2CM6



L	H	B	H2	H3	W
68±0.5	30±0.5	30.2±0.1	20	5	10
Mounting Holes: M6x1 Tap fitted with SS helicoil					
Tightening torque: 15Nm MAX					

TERMINAL STYLE: 2SM6



L	H	B	H2	H3	H4	W
68±0.5	30±0.5	30.2±0.1	16	6.5	10.5	10
Tightening torque: 15Nm MAX						

Americas / EU
Phone: 1-508-996-8561
Email: cdena@cde.com



**CORNELL
DUBILIER**



Asia
Phone: 852-2793-0931
Email: cdeasia@cde.com







HC2

High Power Resonant Capacitors



Frequency Derating

—●— Voltage —■— Current —▲— Power



Americas / EU

Phone: 1-508-996-8561

Email: cdena@cde.com



**CORNELL
DUBILIER**



Asia

Phone: 852-2793-0931

Email: cdeasia@cde.com





HC2

High Power Resonant Capacitors



Frequency Derating

—●— Voltage —■— Current —▲— Power



Americas / EU

Phone: 1-508-996-8561

Email: cdena@cde.com



**CORNELL
DUBILIER**



Asia

Phone: 852-2793-0931

Email: cdeasia@cde.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cornell Dubilier / Knowles:](#)

<u>254HC2800K2CM6</u>	<u>664HC2700K2CM6</u>	<u>245HC2450K2CM6</u>	<u>125HC2600K2CM6</u>	<u>174HC2900K2CM6</u>
<u>334HC2800K2CM6</u>	<u>135HC2600K2CM6</u>	<u>503HC2102K2CM6</u>	<u>504HC2800K2CM6</u>	<u>135HC2600K2SM6</u>
<u>125HC2600K2SM6</u>	<u>174HC2900K2SM6</u>	<u>245HC2450K2SM6</u>	<u>254HC2800K2SM6</u>	<u>334HC2800K2SM6</u>
<u>503HC2102K2SM6</u>	<u>504HC2800K2SM6</u>	<u>664HC2700K2SM6</u>	<u>254HC2A800K2BM6</u>	