

LC5

High Power Resonant Capacitors



FEATURES

High AC Voltage - High Current

APPLICATIONS

Induction Heating - Tank Circuits

KVAR	500
CAPACITANCE TOLERANCE	+/-10%
MAXIMUM CORE TEMPERATURE	+85°C
SURFACE TEMPERATURE	+45°C (Above 45°C the KVAR rating must be de-rated by 2.25%/°C)
CONSTRUCTION	Self-healing
SELF INDUCTANCE	< 3 nH
DIELECTRIC	Polypropylene
FLAME RETARDANT	UL94V0

Standard Part Listing

Capacitance (μF)	VAC	IC PART number	Maximum RMS current (A)	MAX power kvar	Frequency range (kHz)	ESR (mΩ) 100kHz, +25°C	Dimensions (mm)			Terminal Style
							B	H	L	
1.2	1100	125LC5112K5PM8	600	500	55-96	1.5	54	100	100	5PM8
1.4	1100	145LC5112K5PM8	600	500	46-83	1.2	54	100	100	5PM8
3.0	750	305LC5750K5PM8	800	500	47-68	1.1	54	100	100	5PM8
3.3	750	335LC5750K5PM8	800	500	43-62	1.0	54	100	100	5PM8
4.0	900	405LC5900K5PM8	700	500	25-39	0.9	54	100	100	5PM8
5.6	700	565LC5700K5PM8	1000	500	29-57	0.9	54	100	100	5PM8
6.3	700	635LC5700K5PM8	1000	500	26-51	0.8	54	100	100	5PM8
8.5	700	855LC5700K5PM8	1000	500	19-38	0.7	54	100	100	5PM8
10	700	106LC5700K5PM8	1000	500	16-32	0.6	54	100	100	5PM8
21	500	216LC5500K5PM8	1000	500	15	0.4	54	100	100	5PM8
27	550	276LC5550K5PM8	1000	500	10-12	0.3	54	100	100	5PM8
33	500	336LC5500K5PM8	1000	500	10	0.3	54	100	100	5PM8
37	500	376LC5500K5PM8	1000	500	9	0.2	54	100	100	5PM8

Americas / EU

Phone: 1-508-996-8561

Email: cdena@cde.com



**CORNELL
DUBILIER**



Asia

Phone: 852-2793-0931

Email: cdeasia@cde.com



Sep-21

LC5

High Power Resonant Capacitors



LEAD STYLE:5PM8



L	H	B	H2	L2
100 $\pm$ 1.0	100 $\pm$ 1.0	54 $\pm$ 0.5	78 $\pm$ 0.5	78 $\pm$ 0.5
Mounting Holes: M8 Tap				
Tightening torque: 20Nm MAX				

Americas / EU

Phone: 1-508-996-8561

Email: cdena@cde.com



**CORNELL
DUBILIER**



Asia

Phone: 852-2793-0931

Email: cdeasia@cde.com

Sep-21







LC5

High Power Resonant Capacitors



Frequency Derating

— Voltage — Current — Power



Americas / EU

Phone: 1-508-996-8561

Email: cdena@cde.com



CORNELL
DUBILIER




Asia

Phone: 852-2793-0931

Email: cdeasia@cde.com







LC5

High Power Resonant Capacitors



Frequency Derating

— Voltage — Current — Power



Americas / EU
Phone: 1-508-996-8561
Email: cdena@cde.com



**CORNELL
DUBILIER**




Asia
Phone: 852-2793-0931
Email: cdeasia@cde.com

LC5

High Power Resonant Capacitors



Frequency Derating



Americas / EU

Phone: 1-508-996-8561

Email: cdena@cde.com



**CORNELL
DUBILIER**



Asia

Phone: 852-2793-0931

Email: cdeasia@cde.com

Sep-21

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cornell Dubilier:

[BLC550J701B4F](#) [855LC5700K5PM8](#) [216LC5500K5PM8](#) [305LC5750K5PM8](#) [376LC5500K5PM8](#) [405LC5900K5PM8](#)
[565LC5700K5PM8](#) [635LC5700K5PM8](#) [106LC5700K5PM8](#) [145LC5112K5PM8](#) [336LC5500K5PM8](#)
[335LC5750K5PM8](#) [276LC5550K5PM8](#) [125LC5112K5PM8](#)