



0,4 - 2,0

Fluorescent lampholder G5

26.620.2017.50



DESCRIPTION

For enclosed cut-outs: 10 x 20 mm

A pair of lampholders provides a lamp length tolerance compensation of 2 mm

Product name:	Fluorescent lampholder G5
Mounting method 1:	Snap-in / screw mount foot
Lamp center:	36 / 38.5
Material:	Housing: PC Rotor: PBT
T-Marking:	130
Approval:	cULus
Material thickness:	0.5 - 1.5
Front Test:	yes
Rotor:	with
Top Test:	yes
Color:	white
Weight:	5
Pkg.:	500